

# Rittal – The System.

Faster – better – everywhere.



## SZ 2500.314 LED system light

State: 24/07/2025 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2500.314 - LED system light

LED system light – the first light especially for enclosures! Highly innovative LED technology for even more light into the very last corner.



## Features

Model No.	SZ 2500.314
Design	with socket, with motion detector
Benefits	Optimum illumination of the entire enclosure Optionally with clip, screw and magnetic attachment A configuration to suit every application
Design	Motion sensor Socket 90° rotating connector Adjustable light direction Adjustable light distribution
Material	Light body: Extruded aluminium Light cover: Polycarbonate Light ends: PC-ABS
Colour	Enclosure: RAL 7016
Supply includes	Assembly screws
Power consumption	13 W
Connection options	Infeed, 3-pole Through-wiring, 3-pole

# Features

Motion detector	Yes
Overvoltage category	II
Protection class	II (all-insulated)
Light – installation type	Screw-fastening Clip attachment
Rated impulse withstand voltage, phase to earth	2500 V AC
Rated insulation voltage	300 V AC
Installation options	Directly onto the enclosure section with 25 mm pitch pattern
Luminous flux	1,200 lm
Light colour	4000 K (neutral white)
Note	Connection accessories should be ordered separately
Dimensions	Width: 437 mm Height: 85 mm Depth: 44 mm
Operating temperature range	-20 °C...55 °C
Sockets	USA/CDN (type B, NEMA 5-15)
Rated operating voltage	100 V - 125 V, 1~, 50 Hz/60 Hz
Socket version	USA/CDN (type B, NEMA 5-15)
IP protection category to IEC 60529	IP 20
Packs of	1 pc(s).
Net weight	0.6
Gross weight	0.684
Customs tariff number	94054990
EAN	4028177811287
ETIM 9	EC000321
ETIM 8	EC000321
ECLASS 8.0	27189241

# Approvals

---

Approvals

ENEC

UL

---

Explanations

Declaration of conformity

Declaration of conformity UK