

Rittal – The System.

Faster – better – everywhere.



SK 3108.024

Enclosure internal fan

State: 24/08/2025 (Source: [rittal.com/ie-en](https://www.rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3108.024 - Enclosure internal fan

To prevent hot-spots inside the enclosure and support the air routing of active enclosure climate control components.



Features

Model No.	SK 3108.024
Product description	To prevent hot-spots and support the air routing of active enclosure climate control components. Adjustable in two axes. Attached to the frame section. Several fans may be cascaded using the quick-release clamping strip.
Supply includes	Complete unit with axial fan ready for connection Snap-on pivot device Assembly parts
Rated operating voltage	24 V (DC)
Power consumption Pel	With DC: 3.5 W
Rated current max.	With DC: 0.15 A
Packs of	1 pc(s).
Net weight	0.8
Gross weight	0.978
Customs tariff number	84145915
EAN	4028177220508
ETIM 9	EC000320

Features

ETIM 8	EC000320
ECLASS 8.0	27180716

Approvals

Explanations	Declaration of conformity
--------------	---------------------------