## Rittal – The System.

Faster – better – everywhere.





# SK 3166.115 Roof-mounted fans

State: 25/11/2025 (Source: rittal.com/ie-en)



## SK 3166.115 - Roof-mounted fans for VX IT, TS IT

Roof-mounted fan with an exceptionally low noise level of 39 dB(A) and a high volumetric flow (unimpeded air flow 1245 to 1345 m³/h), for use in office environments.

#### **Features**

Model No.	SK 3166.115
Benefits	Simple connection system with C13 IEC 320 socket Energy-efficient speed control with preset characteristic curve Very quiet and therefore suitable for office environments International approvals and multi-voltage capability for worldwide use
Applications	for the office sector
Function principle	The speed-regulated fan modifies output to the actual requirements
Material	Sheet steel, spray-finished
Colour	RAL 9005
Supply includes	1 fan unit Speed control Fully wired ready for connection Assembly parts Installation and Short User's Guide Without roof plate
Rated operating voltage	100 V - 130 V, 1~, 50 Hz/60 Hz
Note on Model No.	Reduction in the specified air throughput to 800 m³/h at 40 Pa counterpressure using two vented base/plinth trim panels
Rated current max.	At 50 Hz: 0.5 A At 60 Hz: 0.5 A
Design	Pre-configured
Dimensions	Width: 470 mm Height: 200 mm Depth: 470 mm
Mounting cut-out	Width:410 mm Depth:410 mm

© Rittal 2025

2

### Features

Protection category to IEC 60 529	IP 20
Temperature control	Speed-controlled fan
Operating temperature range	5 °C55 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 24 W Power consumption L35 L35/60 Hz: 24 W
Air throughput (unimpeded air flow)	1,245 m³/h
Air throughput (at operating point)	800 m³/h
Noise level (at operating point)	39 dB(A)
Pre-fuse	Miniature circuit-breaker/fuse: 10 A
Packs of	1 pc(s).
Net weight	11.267
Gross weight	11.86
Customs tariff number	84145915
EAN	4028177966260
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

## **Approvals**

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3

#### Tender text

SK roof fan 100-130 V, 50-60Hz

Order No. SK 3166.115

Roof fan for active ventilation of an enclosure.

Use, directly in the cut-out integrated in the roof panel of the dimension WxD 410x410 mm.

Applicable e.g. for manufacturer Rittal, enclosure series VX IT, TS IT. Complete unit ready for connection with C 13 cold appliance socket Incl. radial fan, speed controller, fixing material and mounting instructions.

Technical data:

Rated operating voltage:

100-130 V, 1~, 50/60 Hz

Rated power: 24 W at 50/60 Hz

Rated current (max.) at 50/60 Hz: 0.5 A

Fine-wire fuse T 10 A, 250 V, 5 x 20 mm integrated

Air performance free blowing:

1245 m<sup>3</sup>/h, 50/60 Hz

Air performance at operating point:

800 m³/h at 40 Pa, 50/60 Hz

Sound pressure level at operating point: 39 dB (A)

Operating temperature range:

+5°C to + 55°C

Dimensions WxHxD in mm: 470x200x470 mm Protection class according to IEC 60529: IP 20

Material: sheet steel, painted

Color: RAL 9005 Matt, fine structure

Order No. SK 3166.115 Manufacturer: Rittal

© Rittal 2025 4