

Rittal – The System.

Faster – better – everywhere.



SK 3237.118 TopTherm filter fans

State: 10/07/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3237.118 - TopTherm filter fans

Complete fan unit for tool-free mounting on surfaces. Air throughput from 20 - 900 m³/h, standard protection category IP 54.

Features

Model No.	SK 3237.118
Design	wall-mounted
Product description	Fan-and-filter units with diagonal fan technology have superior pressure stability and ensure a more constant air throughput. The diagonal direction of outflow ensures more even heat dissipation from the enclosure.
Product modification	The cover for the connection clamp has not been part of the TopTherm filter fans since May 2024. In testing, it proved not to be necessary to meet the standard, and affects neither function nor operational reliability.
Colour	RAL 9005
Supply includes	Complete unit ready to install, including chopped-fibre filter mat
Fan	Axial, shaded pole motor
Air throughput, unimpeded airflow (with chopped-fibre filter)	At 50 Hz: 20 m ³ /h At 60 Hz: 25 m ³ /h
Air throughput with outlet filter including chopped-fibre filter mat (quantity x order number)	1 x 3237208: 15/18 m ³ /h 2 x 3237208: 16/20 m ³ /h
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz
Power consumption Pel	At 50 Hz: 11 W At 60 Hz: 9 W
Rated current max.	At 50 Hz: 0.12 A At 60 Hz: 0.13 A
Dimensions	Width: 116.5 mm Height: 116.5 mm
Installation depth	43 mm

Features

Mounting cut-out	Cut-out width: 92 mm Cut-out height: 92 mm
IP protection category to IEC 60529	IP 54 with chopped-fibre filter IP 56 with chopped-fibre filter and hose-proof hood
Protection category NEMA	Type 12 with chopped-fibre filter Type 3 Type 3R with chopped-fibre filter and hose-proof hood
Pre-fuse	Miniature circuit-breaker/fuse: 2 A
Note	To increase the air throughput, a pleated filter may optionally be used (see characteristic curve). Suitable for use with fan-and-filter units, roof-mounted fans and outlet filters. With the filter fan 3237.XXX, electrical connection is made via two single wires (length approx. 300 mm) on the unit, for all other filter fans, a screwless spring terminal is used
Service life of fans (L10, 40 °C)	At 50 Hz: 55,000 h At 60 Hz: 60,000 h
Operating temperature range	-15 °C...55 °C
Storage temperature range	-30 °C...70 °C
Noise level	At 50 Hz: 38 dB(A) At 60 Hz: 43 dB(A)
Packs of	1 pc(s).
Net weight	1.2 kg
Gross weight	1.38 kg
Customs tariff number	84145915
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716
Product description	SK Fan-and-filter unit TopTherm, 20/25 m ³ /h, 115 V, 1~, 50/60 Hz, WHD: 116.5 x 116.5 x 16 mm

Approvals

Approvals	30 - KC Korea UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

Fan-and-filter units with diagonal fan technology have superior pressure stability and ensure a more constant air throughput. The diagonal direction of outflow ensures more even heat dissipation from the enclosure

Air throughput (unimpeded air flow): 20 / 25 m³/h

Power consumption: 11 / 9 W

Rated current: 0,12 / 0,1 A

Rated operating voltage: 115 V, 1~, 50/60 Hz

Fan: Axial, shaded pole motor

Dimensions [WxH]: 116,5x116,5 mm

Build depth: 16 mm

Installation depth: 43 mm

Mounting cut-out [WxH]: 92x92 mm

Operating temperature range: -15°C to 55°C

Storage temperature range: -30°C to 70°C

Colour: RAL 9005

Protection category IP to IEC 60 529:

IP 54 with fleece filter

IP 56 with fleece filter and hose-proof hood

Protection category NEMA:

Type 12 with fleece filter

Type 3, 3R with fleece filter and hose-proof hood

Noise level: 38 / 43 db(A)

Service life of fans: 55.000 / 60.000 h

Weight: 0,48 kg