


Rittal – The System.

Faster – better – everywhere.



SK 3245.600 TopTherm filter fans

State: 23/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3245.600 - TopTherm filter fans EMC

Complete fan unit with EMC shielding for tool-free mounting on surfaces. Air throughput from 20 - 900 m³/h, standard protection category IP 54.



Features

| | |
|--|--|
| Model No. | SK 3245.600 |
| Design | wall-mounted EMC |
| Product description | EMC fan-and-filter units offer a high shielding/attenuation effect and meet requirement category 2 to EN 61587-3. |
| Product modification | The cover for the connection clamp has not been part of the TopTherm filter fans since May 2024. In testing, it proved not to be necessary to meet the standard, and affects neither function nor operational reliability. |
| Colour | RAL 7035 |
| Supply includes | Complete unit ready to install, including chopped-fibre filter mat |
| Fan | Diagonal, EC motor |
| Air throughput (unimpeded air flow) | At 50 Hz: 890 m ³ /h At 60 Hz: 890 m ³ /h |
| Air throughput with outlet filter including chopped-fibre filter mat (quantity x order number) | 1 x 3243060: 630/630 m ³ /h 2 x 3243060: 770/770 m ³ /h |
| Rated operating voltage | 200 V - 240 V, 1~, 50 Hz/60 Hz |
| Rated current max. | At 50 Hz: 1.33 A At 60 Hz: 1.33 A |

Features

| | |
|-------------------------------------|--|
| Power consumption Pel | At 50 Hz: 165 W At 60 Hz: 165 W |
| Dimensions | Width: 323 mm Height: 323 mm |
| Installation dimensions | Build depth: 25 mm Installation depth: 130.5 mm |
| Mounting cut-out | Cut-out width: 292 mm Cut-out height: 292 mm |
| Note | To improve energy efficiency and extend the service life of the devices, we recommend the use of thermostats or temperature displays |
| IP protection category to IEC 60529 | IP51 with chopped-fibre filter IP 56 with chopped-fibre filter and hose-proof hood |
| Protection category NEMA | Type 1 Type 12 Type 3 Type 3R with chopped-fibre filter and hose-proof hood |
| Pre-fuse | Miniature circuit-breaker/fuse: 4 A |
| Service life | 59,000 h |
| Operating temperature range | -25 °C...55 °C |
| Storage temperature range | -25 °C...70 °C |
| Noise level | At 50 Hz: 72 dB(A) |
| Packs of | 1 pc(s). |
| Net weight | 3.622 kg |
| Gross weight | 3.822 kg |
| Customs tariff number | 84145915 |
| ETIM 9 | EC000320 |
| ETIM 8 | EC000320 |
| ECLASS 8.0 | 27180716 |
| Product description | SK Fan-and-filter unit TopTherm, 890/890 m ³ /h, 200-240 V, 1~, 50/60 Hz, WHD: 323 x 323 x 25 mm, EMC |

Approvals

| | |
|--------------|---|
| Approvals | CSA UL + C-UL - FTTA UR + C-UR (recognized) |
| Explanations | Declaration of conformity Declaration of conformity UK |

Tender text

EMC fan-and-filter units offer a high shielding/attenuation effect and meet requirement category 2 to EN 61587-3.

Air throughput (unimpeded air flow): 890/890 m³/h

Power consumption 50/60 Hz: 165 / 165 W

Rated power input 50/60 Hz: 1,33 / 1,33 A

Rated operating voltage: 200-240 V, 1~, 50/60 Hz

Diagonal fan: Diagonal, EC-Motor

Dimensions [WxH]: 323x323 mm

Installation depth: 130,5 mm

Build depth: 25 mm

Required mounting cut-out [WxH]: 292x292 mm

Operating temperature range: -25°C to +55°C

Storage temperature range: -25°C to +70°C

Colour: RAL 7035

Protection category IP to IEC 60 529:

IP 51 with fleece filter

IP 56 with fleece filter with hose-proof hood

Protection category NEMA:

Type 1, 12, 3, 3R with fleece filter with hose-proof hood

Noise level 50/60 Hz: 72 dB(A)

Service life 50/60 Hz: 59.000 h

Weight: 3,5 kg