

Rittal – The System.

Faster – better – everywhere.



SK 3311.030 Touchscreen display, colour

State: 14/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

SK 3311.030 - Touchscreen display, colour for LCP Rack/ Inline CW

All relevant operating parameters are displayed directly on the LCP display, to allow directly monitoring of key LCP functions and the implementation of settings.

Features

Model No.	SK 3311.030
Product description	The display offers the opportunity of directly monitoring key functions of the LCP, and implementing settings.
Supply includes	Touchscreen display, colour Connection cable Assembly parts
To fit Model No.	SK 3311.130/230/260/530/540/560/148/238/268/548/538/568 SK 3312.130/230/250/260/530/540/550/560/570 SK 3313.130/230/250/260/530/540/550/560/570/238/268/548/538/ 568 SK 3314.130/230/250/260/530/540/542/550/560/570
Packs of	1 pc(s).
Net weight	0.3 kg
Gross weight	0.373 kg
Customs tariff number	85312040
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712
Product description	SK Touchscreen display, colour, for LCP Rack/Inline CW 3311./3312./3313./3314.xxx

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK

Tender text

SK touchscreen display, colour

for LCP Rack/Inline CW

3311.130/230/260/530/540/560/148/238/268/548/538/568

3312.130/230/250/260/530/540/550/560/570 and

3313.130/230/250/260/530/540/550/560/570/238/268/548/538/568

3314.130/230/250/260/530/540/542/550/560/570

Touchscreen display:

Via the display the user can see all relevant operating parameters of the LCP directly.

The benefit is that the user can recognise at a glance the status of the device and react immediately if necessary.

The following parameters are shown on the display in different levels:

Display of cold air temperature routed to the 19" equipment

Display of hot air temperature dissipated from the 19" equipment

Cooling output

Cooling water inlet / return temperature

Cooling water flow rate

Position of the control valve

Overview of all parameters at a glance

Display of alarm and warning messages

Overview page with IP address of the device (>,<)> software status and contact (may be entered individually)

Change of the set value of the cold air temperature in front of the 19" level may be carried out on the display (blocking possible, if required)

Touchscreen display, supply includes:

Touchscreen display, colour, with assembly parts

4,3" display, 480 x 272 pixels

Resistive touch

Type 280 cd/m²

Operating temperature: -20°C to +70°C

Connection cable