

Rittal – The System.

Faster – better – everywhere.



SK 3478.801

Blue e+ S wall-mounted cooling unit

State: 6/06/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3478.801 - Blue e+ S wall-mounted cooling unit 0.3 kW – 1 kW

Blue e+ S cooling units with tried-and-tested Blue e+ technology are the world's most energy-efficient cooling units. This means they reduce the carbon footprint of your machines and systems. Available in a brand new design with a host of smart functions.

Features

| | |
|--------------------------------------|---|
| Model No. | SK 3478.801 |
| Design | wall-mounted |
| Benefits | Contributes to climate-neutral production with average energy savings of 75% and a reduced carbon footprint Multi-voltage capabilities and country-specific approvals support global usability Smart, simple monitoring via IoT interface User-friendly operation with the Rittal Scan & Service app |
| Material | Sheet steel |
| General colour | RAL 7035 |
| Colour | Enclosure: RAL 7035 Louvred grille: RAL 7012 |
| Supply includes | Assembly parts Fully wired ready for connection (plug-in terminal strip) |
| Options | For remote monitoring and networking of cooling units and chillers in the Blue e+ generation, please use the IoT interface (Model No. 3124.300). Increase machine availability and process reliability with remote monitoring of device data, statuses and system messages. |
| Total cooling output to DIN EN 14511 | Cooling output L35 L35/50 Hz: 0.3 kW Cooling output L35 L35/60 Hz: 0.3 kW Cooling output L35 L50/50 Hz: 0.14 kW Cooling output L35 L50/60 Hz: 0.14 kW |
| Rated operating voltage | 110 V - 240 V, 1~, 50 Hz/60 Hz |

Features

| | |
|---|--|
| Note | Please observe the mounting instructions. By downloading the software, a contract is concluded between the contractual partner and Rittal for the free use of the software in accordance with these licence conditions. Only suitable for use in semi-outdoor areas (see instructions for description) |
| Note on Model No. | Tolerance: 110 V -10% (99 V) and 240 V +10% (264 V) |
| Rated power input | 0.22 kW |
| Air throughput (unimpeded air flow) | External circuit: 366.6 m ³ /h Internal circuit: 366.6 m ³ /h |
| Energy efficiency ratio (EER) 50/60 Hz L35 L35 | Refrigeration factor L35 L35 (EER) 50 Hz: 2.01 Refrigeration factor L35 L35 (EER) 60 Hz: 2.01 |
| Design | wall-mounted |
| Dimensions | Width: 300 mm Height: 570 mm Depth: 159 mm |
| Required mounting cut-out | Cut-out width: 280 mm Cut-out height: 550 mm |
| Protection category to IEC 60 529 | Internal circuit IP 55 |
| Protection category NEMA | UL Type 1 UL Type 12 |
| Refrigerant/cooling medium | Refrigerant: R-1234yf Quantity: 0.135 kg Refrigerant quantity in compression system: 0.08 kg Refrigerant quantity in heat pipe system: 0.055 kg Global Warming Potential (GWP): 0.5 CO ₂ equivalent (CO ₂ e): 0 t |
| Temperature control | e+ controller (factory setting +35 °C) |
| Operating temperature range | -20 °C...60 °C |
| Storage temperature range | -40 °C...70 °C |
| Operating temperature range of refrigerant circuit (active) | 3 °C...60 °C |

Features

| | |
|--|--|
| Heat pipe operating temperature range | -20 °C...45 °C |
| Setting range | 20 °C...50 °C |
| Power consumption Pel | Power consumption L35 L35/50 Hz: 0.15 kW Power consumption L35 L35/60 Hz: 0.15 kW Power consumption L35 L50/50 Hz: 0.17 kW Power consumption L35 L50/60 Hz: 0.17 kW |
| Permissible operating pressure (p. max.) | 32 bar |
| Packs of | 1 pc(s). |
| Net weight | 12.2 kg |
| Gross weight | 12.5 kg |
| PCF per pack (cradle-to-gate) | 77.7 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 84158200 |
| ETIM 8 | EC000855 |
| ECLASS 8.0 | 27180704 |
| Product description | SK Blue e+ S cooling unit, wall-mounted, 0.3 kW, 110-240 V, 1~, 50-60 Hz, sheet steel, WHD: 300 x 570 x 159 mm, R-1234yf |

Approvals

| | |
|--------------|--|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity - F-gas regulation PCF-declaration |