


Rittal – The System.

Faster – better – everywhere.



AS 4050.060

Clamping frame

State: 8/09/2025 (Source: [rittal.com/ie-en](https://www.rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.060 - Clamping frame

Parallel machining of enclosures in the cube machining zone of Perforex machining centres BC and Perforex milling terminals MT for shorter setup times and enhanced productivity.

Features

| | |
|---|--|
| Model No. | AS 4050.060 |
| Design | Pneumatic clamping device |
| Product description | Enables parallel cube machining of enclosures on Perforex machining centres BC and Perforex milling terminals MT. |
| Possible number of terminal Boxes for parallel processing | 3 |
| Note | Use of the clamping frame (Model No. 4050.080) in the machining centre BC (Model No. 4050.230) is only possible with the two-door variant. |
| To fit Model No. | 4050.101 4055.910 4055.911 |
| Suitable for | Perforex BC 1001 HS Perforex MT 1101 Perforex MT 1101 S |
| Dimensions of clampable enclosures max. | Width: 200 mm Height: 300 mm Depth: 300 mm |
| Dimensions of clampable enclosures min. | Width: 85 mm Height: 70 mm Depth: 70 mm |
| Packs of | 1 pc(s). |
| Net weight | 25 |
| Gross weight | 25 |
| Customs tariff number | 84669360 |
| EAN | 4028177804302 |

Features

| | |
|------------|----------|
| ETIM 9 | EC003010 |
| ETIM 8 | EC003010 |
| ECLASS 8.0 | 36609190 |