Rittal – The System.

Faster – better – everywhere.





AS 4050.454 Crimping machine R8 E

State: 5/11/2025 (Source: rittal.com/ie-en)



AS 4050.454 - Crimping machine R8 E

Electrically driven wire stripping and crimping machine for taped wire end ferrules on a reel.





Features

| Model No. | AS 4050.454 |
|--------------------------|--|
| Design | Touchscreen display |
| Product description | Electrically powered wire stripping and crimping machine for taped wire end ferrules on a reel. |
| Benefits | Easy to operate Fast adjustment Flexible use in the workshop Rapid replacement of consumables |
| Technical specifications | Crimping range 0.5 - 2.5 mm² (AWG 20 - 14) Crimping length 8 mm (0.31 in.) Insertion length 40 mm (1.57 in.) |
| Note | The standard crimping form is trapezoid – others available on request |
| Dimensions | Width: 288 mm Height: 230 mm Depth: 345 mm |
| Rated operating voltage | 100 V - 240 V, 1~, 50 Hz/60 Hz |
| Apparent power | 100 VA |
| Compression | Trapezoid crimp |
| Cycle time | 1.8 s |
| Packs of | 1 pc(s). |
| | |

© Rittal 2025

Features

| Net weight | 16 |
|-----------------------|---------------|
| Gross weight | 16 |
| Customs tariff number | 84798997 |
| EAN | 4028177813465 |
| ETIM 9 | EC002778 |
| ETIM 8 | EC002778 |
| ECLASS 8.0 | 36600890 |

© Rittal 2025 3