

**Rittal – The System.**

Faster – better – everywhere.



**AS 4050.887**

**Circular thread milling cutter**

State: 7/04/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.887 - Circular thread milling cutter

Milling cutter for cutting metric threads for Perforex machining centres BC and Perforex milling terminals MT.

## Features

Model No.	AS 4050.887
Product description	Milling cutter for cutting metric threads for Perforex machining centres BC and Perforex milling terminals MT.
Technical specifications	Shaft diameter 12 mm Cutting diameter 10 mm Pitch 1.5 mm Flank angle 60° Cutting length 20 mm Overall length 85 mm
For threads	M12 - M64
Standards	DIN 13-1 metric ISO thread
Machinable material	Steel Stainless steel Cast aluminium Plastic Copper
Packs of	1 pc(s).
Net weight	0.124 kg
Gross weight	0.124 kg
Customs tariff number	82077031
ETIM 9	EC000945
ETIM 8	EC000945
ECLASS 8.0	36609211
Product description	Circular thread milling cutter, 10x1.5, 12 mm