

**Rittal – The System.**

Faster – better – everywhere.



# AS 4055.020

## Manual hydraulic punch

State: 26/03/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4055.020 - Manual hydraulic punch

For punching round, square and rectangular cut-outs.



## Features

Model No.	AS 4055.020
Design	Flexible, with hydraulic hose and separate cylinder
Product description	For punching round, square and rectangular cut-outs.
Benefits	Extend tool life with a built-in overpressure valve Hole punches, hydraulic punches and accessories for making round, square and rectangular cut-outs in steel steel and stainless steel
Material	Aluminium
Supply includes	Manual hydraulic punch Hydraulic screw Ø 19 mm Hydraulic screw Ø 9.5 / 19 mm HSS pilot drill Ø 11 mm Spacer sleeve set (3-part) Plastic case
Hydraulic operation	Round punch up to Ø 82 mm Rectangular punch up to 46 x 86 mm Punching force 75 kN Max. operating pressure 680 bar/9850 psi Hole punch, square, up to 92 x 92 mm
Packs of	1 pc(s).
Net weight	3.4 kg
Gross weight	3.546 kg
Customs tariff number	84678900

# Features

---

ETIM 9	EC001085
ETIM 8	EC001085
ECLASS 8.0	21049046
Product description	Hand hydraulic punch, hose a. cylind.

---