


Rittal – The System.

Faster – better – everywhere.



AS 4055.520

Splitter hole punch, round

State: 30/01/2026 (Source: rittal.com/ie-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

AS 4055.520 - Splitter hole punch, round for sheet steel, with triple splitting

For punching round cut-outs

Features

| | |
|--|---|
| Model No. | AS 4055.520 |
| Design | With triple splitting |
| Product description | |
| Supply includes | Female dies Male dies |
| Machinable material | Sheet steel |
| Maximum machinable material thickness, sheet steel | 2 mm |
| Ø punch | 20.4 mm |
| For threads | M20 |
| Note | When operating with wrenches, tension screws with ball bearings should be used. Other sizes, see splitter hole punch, round, stainless steel |
| Suitable for hydraulic bolt order number | 4055.661 |
| Tension screw (Ø x L) | 9.5 x 50 mm |
| Hydraulic tension screw Ø | 9.5 mm 19 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.075 |
| Gross weight | 0.095 |
| Customs tariff number | 82073010 |
| EAN | 4028177808669 |

Features

ETIM 9 EC000156

ETIM 8 EC000156

ECLASS 8.0 21049047