

Rittal – The System.

Faster – better – everywhere.



AS 4055.580

Splitter hole punch set, M16 to M40

State: 27/08/2025 (Source: [rittal.com/ie-en](https://www.rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.580 - Splitter hole punch set, M16 to M40 for sheet steel, with triple splitting

For punching round cut-outs

Features

| | |
|--|---|
| Model No. | AS 4055.580 |
| Design | With triple splitting |
| Product description | For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch. |
| Supply includes | 5 female dies 5 male dies Plastic case |
| Machinable material | Sheet steel |
| Maximum machinable material thickness, sheet steel | 2 mm 2 mm 2 mm 3 mm 3 mm |
| Ø punch | 16.2 mm 20.4 mm 25.4 mm 32.5 mm 40.5 mm |
| For threads | M16 M20 M25 M32 M40 |
| Note | When operating with wrenches, tension screws with ball bearings should be used. |

Features

| | |
|--|---------------|
| Suitable for hydraulic bolt order number | 4055.661 |
| | 4055.661 |
| | 4055.661 |
| | 4055.663 |
| | 4055.663 |
| Packs of | 1 pc(s). |
| Net weight | 1 |
| Gross weight | 1.039 |
| Customs tariff number | 82034000 |
| EAN | 4028177808836 |
| ETIM 9 | EC002121 |
| ETIM 8 | EC002121 |
| ECLASS 8.0 | 21044719 |