


**Rittal – The System.**

Faster – better – everywhere.



# VX 5301.516

## Castor module

State: 26/06/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 5301.516 - Castor module for VX, VX IT

For easy movement directly at the point of use, even with fully configured enclosures.

## Features

Model No.	VX 5301.516
Supply includes	1 transport module with 2 castors 1 transport module with 2 castors, fixed Assembly parts
Dimensions	Width: 556 mm Height: 82.5 mm Depth: 203 mm
Assembly instruction	The base area must be open at the mounting points
To fit	Enclosure type: VX: = 600 mm Enclosure type: VX IT
Load capacity	Max. admissible load: Static 15,000 N Max. admissible load: Dynamic 10,000 N
Note	The maximum admissible load capacity (dynamic) of 10,000 N refers to rolling over flat ground.
Packs of	1 pc(s).
Net weight	10 kg
Gross weight	10.3 kg
Customs tariff number	83024900
ETIM 9	EC002621
ECLASS 8.0	27189262
Product description	Castor module for VX IT, for W: 600 mm, for easy movement directly at the point of use, for mounting directly on the enclosure.

## Tender text

Castor module for W: 600 mm

For easy movement on site, can be mounted directly on the IT rack.

Scope of delivery:

1 transport module with 2 castors

1 transport module with 2 baying clamps, fixed

Assembly parts