

Rittal – The System.

Faster – better – everywhere.



DK 7320.700

Handles, electromagnetic

State: 17/04/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7320.700 - Handles, electromagnetic for CMC III and IoT Interface

Handles may be integrated into various enclosure systems.

Features

Model No.	DK 7320.700
Design	Ergoform-S handle
Product description	For control and monitoring via a central CMC III type control unit and IoT interface.
Benefits	Autonomous access administration and handle release via numerical code or transponder card Administration of authorisations and remote opening via the network Integral Web interface and connection to central management systems via the control unit Record of each time the door is opened, with time stamp
Applications	Central access administration via the network - no need for keys or lock systems Free-standing network racks with sensitive IT systems Data centres with enhanced security requirements or colocation/ hosting applications
Colour	RAL 7035
Supply includes	Connection cable (3 m) with RJ 12 connector
Lock type	Electromagnetic
Rated current max.	0.1 A
No. of participants per IoT interface (max.)	16
No. of participating PU compact (max.)	2
No. of participating PU (max.)	16
Number subscribers per PDU note	Max. 5 p. for power supply with PoE

Features

Operating temperature range	5 °C...40 °C
Packs of	1 pc(s).
Net weight	0.76 kg
Gross weight	0.76 kg
Customs tariff number	83024110
ETIM 9	EC000327
ECLASS 8.0	27409217
Product description	DK CMC III handle, electromagnetic, Ergoform-S handle with master key function for TE, access control via CMC III Processing Unit, with position sensor for monitoring the manual handle, RAL 7035

Tender text

Ergoform-S handle with electromagnetic lock for CMC-TC
Ergoform-S handle with electromagnetic lock
for CMC-TC for FR, PS, TC, VR, TE.

With position sensor for monitoring the handle and
electromagnetic lock unit for access control.

The handle contains an integrated identifier so that
it is automatically detected and set up by the
CMC-TC system. It is connected to the access unit.

Technical specifications:

Rated voltage: 24 V DC

Rated current: max. 100 mA

Temperature application range: +5 °C ... +40 °C

Pack of 1