



# Rittal – The System.

Faster – better – everywhere.



## DK 7979.615 PDU local metered

State: 14/07/2025 (Source: [rittal.com/ie-en](https://www.rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7979.615 - PDU local metered

High-end power distribution with local measurement of consumption data. Ideally suited for use in modern server racks and colocation data centres.

## Features

|                                    |   |
|------------------------------------|---|
| Model No.                          | DK 7979.615   |
| Design                             | Blue  |
| Product description                | The PDU with local power measurement is equipped with one display per phase (two displays in total) and supports superior phase loads in the colocation data centre.                  |
| Benefits                           | Integral measurement of current (A); active power (kW); voltage (V); frequency (Hz); power (kWh) and phase angle (°)<br>Measurement accuracy of $\pm 2\%$                             |
| Technical specifications           | Error-tolerant PDU power supply redundant across all phases<br>Connection cable, with connector, 3 m, H05VV-F3G4 mm <sup>2</sup><br>Voltage V, current A, frequency Hz<br>LCD display |
| Function principle                 | Measurement per phase or infeed   |
| Material                           | Aluminium, spray-finished, blue, similar to RAL 5010<br>Cover: Plastic PA 6 GF30, black, similar to RAL 9005  |
| Supply includes                    | PDU with local measurement, 32 A, 1-phase, blue<br>2 angle brackets   |
| Measurement functions, description | Measurement per phase or infeed   |
| Dimensions                         | Width: 44 mm<br>Depth: 47 mm<br>Length: 1,308 mm  |
| No. of sockets and type            | 24 x C13 / 6 x C19<br>IEC/EN/60320/C13<br>IEC/EN/60320/C19  |

# Features

|                                   |   |
|-----------------------------------|---|
| Sockets                           | 24 x C 13<br>6 x C 19<br>2-pole with protective contact, black                                      |
| Rated operating voltage           | 230 V, 50 Hz/60 Hz  |
| Rated current (max.)              | 32 A  |
| Power consumption                 | 7.4 kW  |
| Infeeds                           | Qty.: 1<br>Phases per infeed: 1~  |
| Length of connection cable        | 3 m   |
| Type of electrical connection     | CEE   |
| Directives                        | EMC directive 2014/30/EU<br>Low Voltage Directive 2014/35/EU  |
| Operating temperature range       | 5 °C...45 °C  |
| Ambient humidity (non-condensing) | 5...95 %  |
| Storage temperature range         | -5 °C...60 °C   |
| To fit                            | Enclosure type: VX IT enclosure frame: ≥ 1,800 mm<br>Enclosure type: TX Colocation Rack: ≥ 1,800 mm |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 3.5   |
| Gross weight                      | 3.5   |
| Customs tariff number             | 85366990  |
| EAN                               | 4028177976269   |
| ETIM 9                            | EC002762  |
| ETIM 8                            | EC002762  |
| ECLASS 8.0                        | 27142606  |

## Tender text

Rittal PDU local metered Model No.: DK 7979.615  
PDU local metered 32A/1P CEE 24xC13 / 6xC19  
Compact power distributor for deployment in IT server  
and network enclosures.  
Robust aluminum housing with permanently  
mounted output slots, IEC 60320/C13 or  
IEC 60320/C19.  
A fixed-mounted connection cable with CEE connector  
makes the PDU available for immediate deployment.  
The PDU metered has extensive measurement functions  
for the current and power monitoring.  
The integral TFT colour display enables quick access  
to the electrical consumption data.  
The warranty for proper operation is 24 months.  
Technical specifications PDU local metered:  
Input voltage range (L1/N/PE): 230 VAC, 50-60Hz  
input current: 32A  
No. of phases: 1  
Number of slots type IEC 60320/C13 (total): 24  
Number of slots type IEC 60320/C13  
(per fuse): 12  
Number of slots type IEC 60320/C19 (total): 6  
Number of slots type IEC 60320/C19  
(per fuse): 3  
No. of circuit breakers: 2  
Hydraulic-magnetic protective circuit-breaker: 16 A  
Connector PDU input:  
EN 60309 / CEE  
Length of connection cable: 3m  
Connection cable type: H05VV-F  
No. of wires: 3  
Cable cross-section: 4 mm<sup>2</sup>  
PDU housing width: 44mm  
PDU housing depth: 47mm  
PDU housing height: 1308mm  
PDU material: Aluminum, painted blue RAL 5010  
PDU mounting adaptor included  
Measurement functions: Measurement per fuse:  
Values recorded (per fuse):  
Voltage (V), current (A), frequency (Hz), Power factor,  
active energy (kWh), Active power(kW)  
Voltage measuring range: 90V - 255V

Voltage resolution 0.1V

Current measuring range 0 - 16A/32A

Current resolution 0.1A

Measuring accuracy typ.  $\pm 2\%$

Conformity: CE

Protection category: IP 20

Storage temperature: -20 °C to +60 °C

Ambient temperature: +5°C to +45°C

Ambient humidity <80% rel. humidity, non-condensing

Type: Rittal PDU local metered, Model No.: DK 7979.615