

Rittal – The System.

Faster – better – everywhere.



VX 7993.122

Bayed enclosure system VX25

State: 30/05/2025 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 7993.122 - Bayed enclosure system VX25 BMW AG

Group standard

Valid in all BMW AG component and car factories. VX25 enclosures with 200 mm high base/plinth, for TMO.

Features

| | |
|---------------------|--|
| Model No. | VX 7993.122 |
| Product description | Valid in all BMW AG component and car factories. VX25 enclosures with 200 mm high base/plinth, for TMO. |
| Material | Enclosure frame: Sheet steel, 1.5 mm Roof: Sheet steel, 1.5 mm Door: Sheet steel, 2.0 mm Rear panel: Sheet steel, 1.5 mm Gland plates: Sheet steel, 1.5 mm Mounting plate: Sheet steel, 3.0 mm |
| Surface finish | Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate and gland plates: Zinc-plated |
| Colour | RAL 7035 |
| Supply includes | Door(s) with fitted 180° hinges 8618.330 Door(s) with fitted comfort handle for profile half-cylinders 8618.250 including fitted adaptor kit for double-bit lock insert 7993.200 Base/plinth height: 200 mm, consisting of corner pieces and base/plinth components front and rear 8660.02X, height of base/plinth trim panels 2 x 100 mm at the front and 1 x 200 mm at the rear With zinc-plated mounting plate, mounted in the rearmost position in the final raster hole With LED system light 2500.220, 24 V at the front, with infeed 2500.410 and with fitted door-operated switch 2500.460 |
| Dimensions | Width: 1,200 mm Height: 2,000 mm Depth: 600 mm |

Features

| | |
|-----------------------------------|---------------------|
| Height including base/plinth | 2,200 mm |
| Dimensions mounting plate (W x H) | 1,099 mm x 1,896 mm |
| Number of doors | 2 |
| Packs of | 1 pc(s). |
| Net weight | 191 |
| Gross weight | 204 |
