

# Rittal – The System.

Faster – better – everywhere.



## VX 7993.916

## Bayed enclosure system VX25

State: 10/06/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 7993.916 - Bayed enclosure system VX25 Mercedes-Benz Integra Standard

Daimler Integra enclosure with rear door or with plug-in rear panel, without mounting plate, for installing a wiring system.

## Features

|                     |   |
|---------------------|---|
| Model No.           | VX 7993.916   |
| Design              | With rear door  |
| Product description | Stable symmetrical extrusion frame, consisting of rolled hollow sections with all-round 25 mm DIN pitch pattern of holes at all section levels, horizontal and vertical. Extrusions with two mounting levels for space-saving interior installation, identical punched sections for mounting on the vertical and horizontal frame sections, mounting levels accessible from outside, integral reinforcements for stable fixing to the floor. Simple and stable baying to all sides with a minimum of parts. 3-part gland plate, removable and exchangeable, fitted. Doors with foamed-in seal and locking rod, with a floor clearance of 25 mm at the bottom. |
| Material            | Enclosure frame: Sheet steel, 1.5 mm<br>Roof: Sheet steel, 1.5 mm<br>Rear panel: Sheet steel, 1.5 mm<br>Gland plates: Sheet steel, 1.5 mm<br>Door: Sheet steel, 2.0 mm  |
| Surface finish      | Enclosure frame: Dipcoat-primed<br>Enclosure panels: Dipcoat-primed, powder-coated<br>Gland plates: Zinc-plated<br>Tubular door frame, zinc-plated  |
| Colour              | RAL 7035  |

# Features

---

|                                   |  |
|-----------------------------------|--|
| Supply includes                   | Enclosure frame<br>Door(s)<br>Roof plate screw-fastened with four eyebolts 2568.000<br>Gland plates<br>without mounting plate<br>Front door with square tubular door frame, with fitted 180° hinges 8618.330 and fitted double-bit lock insert 8618.306.<br>Rear door with square tubular door frame, with fitted 130° hinges and fitted double-bit lock insert 8618.306.<br>Potential equalisation of the roof, side panels and gland plates is achieved automatically during assembly via contact elements |
| Dimensions                        | Width: 600 mm<br>Height: 2,000 mm<br>Depth: 500 mm   |
| Protection category to IEC 60 529 | IP 55  |
| Number of doors                   | 1  |
| Packs of                          | 1 pc(s).   |
| Customs tariff number             | 94032080   |