Rittal – The System.

Faster - better - everywhere.





SV 9340.510 **OM** adaptors

State: 17/11/2025 (Source: rittal.com/ie-en)



SV 9340.510 - OM adaptors with spring terminals



Features

| Model No. | SV 9340.510 |
|---|---|
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | Chassis: RAL 7035 |
| Rated current max. | 32 A |
| Rated operating voltage | 690 V, 3~ |
| For bar systems with centre-to- centre spacing | 60 mm |
| Support rail type | without support frame, 1 x TS 45C |
| Number of poles | 3-pole |
| Dimensions | Width: 45 mm Height: 208 mm |
| Connection of round conductors | 1.5 - 6 mm² |
| Support rails Qty/height | 1 / 10 mm |
| To fit busbars | Height: 5, 10 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.231 |
| Gross weight | 0.24 |
| Copper weight (kg per piece) | 0.027 |

© Rittal 2025

Features

| Customs tariff number | 85369095 |
|-----------------------|---------------|
| EAN | 4028177502611 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| Approvals | ABS DNV-GL Lloyds Register of Shipping |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |

Tender text

OM adaptor 32 A

OM adaptor 32 A with tension spring clamp, 3-pole, for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications
Construction width: 45 mm

Length: 208 mm Support frame: -

Support frame support: -

PinBlock: -

Connector outlet: -

Support rail: 1 with anti-slip guard

System:

Rittal RiLine60

© Rittal 2025