


Rittal – The System.

Faster – better – everywhere.



SV 9342.321 Connection block

State: 5/07/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9342.321 - Connection block

For connecting round conductors and laminated copper bars. Suitable for busbars 12 x 5 to 30 x 10 mm and PLS 800/1600.

Features

Model No.	SV 9342.321
Product description	Suitable for busbars 12 x 5 to 30 x 10 mm and PLS 800/1600.
Material	Punched section: Polyamide Cover: ABS Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Supply includes	3 terminals including cover
Clamping area for laminated copper bars with 5 mm bar thickness (W x H)	65 x 27 mm
Clamping area for laminated copper bars with 10 mm bar thickness (W x H)	65 x 22 mm
Cable outlet	Top/bottom
Rated current max.	1,600 A
Electrical ratings UL (SCCR)	65 kA - 480 V, circuit breaker max. 1200 A, DIVQ/7 65 kA - 600 V, Fuse Class L max. 1600 A, JDDZ/7
Note	With overvoltage category III, a rated operating voltage of 1,000 V (AC) is achieved. When using the terminal on 2-pole busbar systems (SV 9340.040), the terminal must be rotated through 180° for connection to the PE busbar.
Dimensions	Width: 85 mm Height: 88 mm
Packs of	3 pc(s).
Net weight	2.1 kg

Features

Gross weight	2.197 kg
Copper weight (kg per piece)	0.136
Customs tariff number	85369095
ETIM 9	EC002270
ECLASS 8.0	27400613
Product description	SV Connection block, 1600 A, 690 V, 1-pole, cable outlet top/bottom, clamping area WH: 65x22/27 mm

Approvals

Approvals	ABS Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

Terminal block 1-pole
Terminal block 1-pole, cable outlet top / bottom
for busbar thickness 5 / 10 mm and PLS 800 / 1600
Type of connection
Clamping area for laminated copper bars for
5 mm bar thickness: 65 x 27 mm
Clamping area for lamintate copper bars for
10 mm bar thickness: 65 x 22 mm
System:
Rittal RiLine60