

Rittal – The System.

Faster – better – everywhere.



VX 8617.570

Partial mounting plates

State: 23/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8617.570 - Partial mounting plates for VX, VX SE, PC, IW

To accommodate additional components inside the enclosure. Partial mounting plates can be used extremely flexibly, providing a platform for a diverse range of applications.

Features

Model No.	VX 8617.570
Product description	To accommodate additional components inside the enclosure. Partial mounting plates can be used extremely flexibly, providing a platform for a diverse range of applications.
Material	Sheet steel, 2.5 mm
Surface finish	Zinc-plated
Supply includes	Assembly parts
To fit door width	800 mm
Installation options	For optional installation either upright as a vertical mounting surface, or flat as a horizontal base. Attach directly onto the enclosure section With a set forward configuration, attachment is via punched sections with mounting flanges at any mounting level in the enclosure For multi-level installation one behind the other, partial mounting plates may be vertically hinged, via hinge attachment, to allow rapid access to the levels behind.
Note	Adaptor rail VX is required for installing in VX SE, PC, IW
Dimensions	Width: 700 mm Depth: 400 mm
To fit enclosure type	VX VX SE PC

Features

To fit	Enclosure type: VX VX SE PC Width: = 800 mm Depth: = 500 mm = 800 mm
Packs of	1 pc(s).
Net weight	7 kg
Gross weight	7.3 kg
PCF per pack (cradle-to-gate)	28.3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
ETIM 9	EC000213
ECLASS 8.0	27409216
Product description	VX Partial mounting plate, dimensions: 700x400 mm