


Rittal – The System.

Faster – better – everywhere.



RX 9360.110 RiLineX basic module

State: 19/08/2025 (Source: [rittal.com/ie-en](https://www.rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.110 - RiLineX basic module

RiLineX basic module, 3-pole, width 100 mm, with integrated busbar support suitable for top mounting, for the modular RiLineX board. Supports the integration of flat bars from 15 x 5 mm to 30 x 10 mm. End-to-end contact hazard protection up to IP 2XB, upgradable to IP 4X. The basic module comprises a base section including busbar support and a top section for contact hazard protection. When compiling a complete solution from basic modules, end modules are additionally required.

Features

| | |
|-------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | RX 9360.110 |
| Benefits | Scalable system lengths with basic modules Simple assembly Scalable rated currents thanks to variable busbar cross-sections Tested short-circuit resistance up to 65 kA Suitable for applications up to 1000 V AC and up to 1500 V DC Extensive range of system accessories Contact hazard protection up to IP 2XB, upgradable to IP 4X Tested and certified to IEC and UL Simple extension and baying |
| Material | Polyamide (PA 6) Fire protection corresponding to UL 94 |
| Colour | RAL 35745 RAL 9005 |
| Supply includes | Basic module base section Basic module (contact hazard protection cover) Assembly screws |
| IP protection category to IEC 60529 | IP 2XB |
| Standards | IEC/EN 61439-1 UL 508 |
| Rated current max. | 800 A |
| Note | Busbars are not included with the supply |

Features

| | |
|-----------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Electrical ratings UL (SCCR) | 65 kA - 600 V, RMS 100 kA - 600 V, Fuse Class L max. 1600 A, JDDZ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7 |
| Centre-to-centre spacing of busbars | 60 mm |
| Rated impulse withstand voltage U _{imp} | 12 kV |
| Rated voltage | 1,000 V AC 600 V AC (UL) 1,500 V DC 600 V DC (UL) |
| Rated insulation voltage | 1,000 V AC 1,500 V DC |
| Rated short-term withstand current/t | 65 kA/500 ms |
| Overvoltage category | 4 |
| Contamination level | 3 |
| Number of poles | 3-pole |
| Fundamental frequency | 50...60 Hz |
| Ambient humidity (non-condensing) | 10...90 % |
| To fit busbars | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Operating temperature range | -5 °C...55 °C |
| Storage temperature range | -25 °C...75 °C |
| Dimensions | Width: 100 mm Height: 246 mm Depth: 49 mm |
| Packs of | 6 pc(s). |
| Net weight | 3 |

Features

| | |
|-----------------------|---------------|
| Gross weight | 3.292 |
| Customs tariff number | 85369010 |
| EAN | 4028177997295 |
| ETIM 9 | EC001900 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |