

**Rittal – The System.**

Faster – better – everywhere.



**RX 9360.535**

**RiLineX CB component adaptor**

State: 8/07/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.535 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 630 A) for 60 mm busbar systems. The device width is 145 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. The cable outlet is easily converted to the top or bottom to suit individual requirements.



## Features

|                                     |   |
|-------------------------------------|---|
| Model No.                           | RX 9360.535   |
| Design                              | Easy Fix  |
| Benefits                            | Direct mounting of moulded-case circuit-breakers (MCCBs) on the board<br>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm<br>Fast, simple pre-assembly of standard market switch types outside of the enclosure |
| Material                            | Polyamide (PA 6)<br>Fire protection corresponding to UL 94  |
| Colour                              | RAL 9005<br>RAL 35745   |
| Supply includes                     | 3 terminal covers   |
| IP protection category to IEC 60529 | IP 2XB  |

# Features

|   |   |
|---|---|
| Rated impulse withstand voltage<br>Uimp | 8 kV  |
| Rated voltage                           | 690 V AC<br>600 V AC (UL)   |
| Rated insulation voltage Ui             | 1,000 V   |
| Contamination level                     | 3   |
| Number of poles                         | 3-pole  |
| Cable outlet                            | Top/bottom  |
| Type of electrical connection           | Screw M10   |
| Cross-section                           | 29 mm <sup>2</sup><br>6 mm <sup>2</sup>   |
| To fit manufacturer (model)             | Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor. |
| To fit busbar system                    | RiLineX<br>RiLine60   |
| Fundamental frequency                   | 50...60 Hz  |
| Ambient humidity (non-condensing)       | 10...90 %   |
| To fit busbars                          | 15 x 5/10<br>20 x 5/10<br>30 x 5/10   |
| Operating temperature range             | -25 °C...55 °C  |
| Storage temperature range               | -25 °C...75 °C  |
| Dimensions                              | Width: 145 mm<br>Height: 325.8 mm<br>Depth: 76.4 mm   |
| Fire load                               | 22.239 MJ/m <sup>2</sup>  |
| Packs of                                | 1 pc(s).  |
| Net weight                              | 5 kg  |
| Gross weight                            | 5.206 kg  |

# Features

---

|                               |  |
|-------------------------------|--|
| Copper weight (kg per piece)  | 2.64   |
| PCF per pack (cradle-to-gate) | 30.05  |
| Customs tariff number         | 85369095   |
| ETIM 9                        | EC001531   |
| Product description           | RiLineX CB component adaptor (3-pole, max. 630 A) for 60 mm busbar systems. The device width is 140 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting. The cable outlet is easily converted to the top or bottom to suit individual requirements. |

# Approvals

---

|              |  |
|--------------|--|
| Approvals    | UL + C-UL (listed)                           |
| Explanations | Declaration of conformity<br>PCF-declaration |

# Tender text

RiLineX CB component adaptor (Easy-Fix)

RiLineX CB component adaptor  
for 60 mm busbar systems.

The switch mounting pattern is easily  
adjusted for fastening using two  
adjustment discs integrated into the adapter.

For voltages up to 690 V AC and 690 V DC.

IEC and UL approved.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm x 5/10 mm

Rated current: 630 A

Connection: 290 mm<sup>2</sup>

Cable outlet: top/bottom

Dimensions: 145 mm x 325 mm x 76 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9360535