


Rittal – The System.

Faster – better – everywhere.



RX 9363.310

RiLineX Fuse-switch disconnecter

State: 20/07/2025 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9363.310 - RiLineX Fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 3 for mounting plates. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M10 screw terminal connection.

Features

| | |
|-------------------------------|---|
| Model No. | RX 9363.310 |
| Design | For mounting plate assembly |
| Benefits | Cover: can be locked and prepared for a lead seal Voltage test through separate opening Tool-free changeover of the cable outlet Park position for simpler maintenance work High rated voltage 800 V ready All variants also available with electronic fuse monitoring |
| Material | Polyamide (PA 6) Fire protection corresponding to UL 94 Contact tracks: Electrolytic copper, silver-plated |
| Colour | RAL 9005 RAL 35745 |
| for mounting plate assembly | Yes |
| Cable outlet | Top/bottom |
| Type of electrical connection | Screw M10 |
| Rated insulation voltage | 1,000 kV |
| Rated operating current max. | 630 A |
| Rated operating voltage | 690 V AC |
| For NH size | 3 |
| Test specification | IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts) |

Features

| | |
|-------------------------------------|--|
| Dimensions | Width: 250 mm Height: 299 mm Depth: 130 mm |
| Operating temperature range | -5 °C...35 °C |
| Storage temperature range | -25 °C...70 °C |
| Number of poles | 3-pole |
| Contamination level | 3 |
| IP protection category to IEC 60529 | IP 2XB |
| Power dissipation (max.) | 84 W |
| Packs of | 1 pc(s). |
| Net weight | 3.8 |
| Gross weight | 3.882 |
| Copper weight (kg per piece) | 1.68 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001040 |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|