

# Rittal – The System.

Faster – better – everywhere.



## RX 9363.315

# RiLineX NH fuse-switch disconnecter

State: 5/04/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9363.315 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 3 for mounting plates. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M10 screw terminal connection. Includes electronic fuse monitoring.

## Features

|                                |                                                                                                                                                                                                                                                     |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                      | RX 9363.315                                                                                                                                                                                                                                         |
| Design                         | For mounting plate assembly                                                                                                                                                                                                                         |
| Benefits                       | Cover: can be locked and prepared for a lead seal<br>Voltage test through separate opening<br>Tool-free changeover of the cable outlet<br>Park position for simpler maintenance work<br>All variants also available with electronic fuse monitoring |
| Material                       | Polyamide (PA 6)<br>Fire protection corresponding to UL 94<br>Contact tracks: Electrolytic copper, silver-plated                                                                                                                                    |
| Colour                         | RAL 9005<br>RAL 35745                                                                                                                                                                                                                               |
| Supply includes                | Connectors for electronic fuse monitoring                                                                                                                                                                                                           |
| for mounting plate assembly    | Yes                                                                                                                                                                                                                                                 |
| Cable outlet                   | Top/bottom                                                                                                                                                                                                                                          |
| Type of electrical connection  | Screw M10                                                                                                                                                                                                                                           |
| Fuse inserts                   | NH 3                                                                                                                                                                                                                                                |
| Rated insulation voltage $U_i$ | 1,000 kV                                                                                                                                                                                                                                            |
| Rated operating voltage        | 690 V AC                                                                                                                                                                                                                                            |
| For NH size                    | 3                                                                                                                                                                                                                                                   |
| Test specification             | IEC/DIN EN 60 947-3<br>DIN EN 60 269-2 (fuse inserts)                                                                                                                                                                                               |

# Features

---

|                                     |                                                                                                                                                                                                                                                                                                                                                                                           |
|-------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Dimensions                          | Width: 250 mm<br>Height: 348.6 mm<br>Depth: 128.7 mm                                                                                                                                                                                                                                                                                                                                      |
| Operating temperature range         | -5 °C...35 °C                                                                                                                                                                                                                                                                                                                                                                             |
| Storage temperature range           | -25 °C...70 °C                                                                                                                                                                                                                                                                                                                                                                            |
| Number of poles                     | 3-pole                                                                                                                                                                                                                                                                                                                                                                                    |
| Contamination level                 | 3                                                                                                                                                                                                                                                                                                                                                                                         |
| with electronic fuse monitoring     | Yes                                                                                                                                                                                                                                                                                                                                                                                       |
| IP protection category to IEC 60529 | IP 2XB                                                                                                                                                                                                                                                                                                                                                                                    |
| Fire load                           | 50.46 MJ/m <sup>2</sup>                                                                                                                                                                                                                                                                                                                                                                   |
| Heat loss max.                      | 84 W                                                                                                                                                                                                                                                                                                                                                                                      |
| Packs of                            | 1 pc(s).                                                                                                                                                                                                                                                                                                                                                                                  |
| Net weight                          | 4.21 kg                                                                                                                                                                                                                                                                                                                                                                                   |
| Gross weight                        | 4.216 kg                                                                                                                                                                                                                                                                                                                                                                                  |
| Copper weight (kg per piece)        | 1.68                                                                                                                                                                                                                                                                                                                                                                                      |
| Customs tariff number               | 85369095                                                                                                                                                                                                                                                                                                                                                                                  |
| ETIM 9                              | EC001040                                                                                                                                                                                                                                                                                                                                                                                  |
| Product description                 | RiLineX NH fuse-switch disconnecter in size 3 for mounting plates. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Size M10 screw terminal connection. Includes electronic fuse monitoring. |

# Approvals

---

|              |                                              |
|--------------|----------------------------------------------|
| Explanations | Declaration of conformity<br>PCF-declaration |
|--------------|----------------------------------------------|

# Tender text

RiLineX NH fuse-switch disconnecter (size 3 mit ESÜ)

NH fuse-switch disconnecter for mounting on mounting plate.

Other properties include sealability,

Voltage test via separate openings,

Parking position for the cover and lockability with padlocks in the open position (service case).

Rated voltage 690 V AC.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm

Busbar dimensions: 5/10 mm

Rated current: 630 A

Type of electrical connection: Screw M10

Cable outlet: top/bottom

Dimensions: 250 mm x 348 mm x 134 mm (BxHxT)

Feature: Electronic fuse monitoring

Manufacturer: Rittal GmbH & Co. KG

Type: 9363315