Rittal – The System.

Faster – better – everywhere.





KEL 9306.000 Ex enclosures

State: 4/11/2025 (Source: rittal.com/ie-en)



KEL 9306.000 - Ex enclosures stainless steel, empty enclosure with screw-fastened cover

Ex enclosure with screw-fastened cover, stainless steel







Features

| Model No. | KEL 9306.000 | |
|-----------------|--|--|
| Design | Ex enclosures | |
| Applications | Zone 1 and 2 or 21 and 22 to 2014/34/EC | |
| | Ambient temperature range: -30 °C+80 °C | |
| | The specified temperatures may be limited by the installed equipment | |
| | Explosion protection category to EN 60 079: Equipment protection | |
| | thanks to increased safety (Ex e), equipment protection thanks to | |
| | enclosure (Ex tb) | |
| Material | Enclosure: Stainless steel 1.4301 (AISI 304) | |
| | Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in | |
| | silicone seal | |
| Surface finish | Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 μm | |
| Supply includes | Enclosure | |
| | Cover | |
| Dimensions | Width: 300 mm | |
| | Height: 300 mm | |
| | Depth: 120 mm | |

© Rittal 2025

Features

| Certificate IEC EX PTB 09.0033U | Yes |
|--------------------------------------|-----------------------------------|
| Certificate PTB 03 ATEX 1013U | Yes |
| Basic material | Stainless steel 1.4301 (AISI 304) |
| IP protection category to IEC 60 529 | IP 66 |
| Packs of | 1 pc(s). |
| Net weight | 3.7 |
| Gross weight | 3.9 |
| Customs tariff number | 94032080 |
| EAN | 4028177138643 |
| ETIM 9 | EC002503 |
| ECLASS 8.0 | 27180502 |

Approvals

| Approvals | ATEX | |
|-----------|-----------|--|
| | ATEX QA | |
| | IECEx | |
| | IECEx QAR | |

© Rittal 2025 3