Rittal – The System.

Faster - better - everywhere.





SV 9340.950 Bus-mounting fuse base D-Switch

State: 3/11/2025 (Source: rittal.com/ie-en)



SV 9340.950 - Bus-mounting fuse base D-Switch

With integral visual fuse monitoring via flashing indicator and operating status display.

Features

| Model No. | SV 9340.950 | | |
|---|---|--|--|
| Material | Polyamide Fire protection corresponding to UL 94-V0 | | |
| Colour | Chassis: RAL 7035 Fuse holder: RAL 7001 | | |
| Supply includes | Retaining springs for D 01 and 10 x 38 mm fuses | | |
| Note | Wire end ferrules should be used with fine wire conductors | | |
| For bar systems with centre-to- centre spacing | 60 mm | | |
| Type of electrical connection | Box terminal | | |
| Fuse inserts | D 01 (with reducer) D 02 (with Neozed adaptor sleeve) 10 x 38 (with retaining spring) | | |
| Fuse inserts footnote | When using D 01 and 10 x 38 mm fuses, reducers must be used. Use of D 01 fuses optionally possible with adaptor sleeve for D 0 base/plinths. | | |
| Rated operating current max. | 63 A | | |
| Rated operating voltage | 400 V, 3~ | | |
| Note | For the use of fuse inserts to EN 60 269-3 (DIN VDE 0636-3) With integral visual fuse monitoring via flashing indicator and operating status display as well as cable routing for conductors to 6 mm ² | | |
| Test specification | IEC/DIN EN 60 947-3 | | |
| Dimensions | Width: 27 mm Height: 226 mm | | |
| Connection of round conductors | 1.5 - 25 mm² | | |

© Rittal 2025

Features

| To fit busbars | Height: 5, 10 mm |
|------------------------------------|------------------|
| Voltage range for indicator lights | 100 - 400 V |
| Number of poles | 3-pole |
| Packs of | 3 pc(s). |
| Net weight | 0.975 |
| Gross weight | 1.04 |
| Copper weight (kg per piece) | 0.066 |
| Customs tariff number | 85369095 |
| EAN | 4028177603400 |
| ETIM 9 | EC001046 |
| ECLASS 8.0 | 27371402 |

Approvals

|--|--|--|

© Rittal 2025 3