

Rittal – The System.

Faster – better – everywhere.



SV 9666.350

Connection terminal block

State: 7/04/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9666.350 - Connection terminal block

For connecting copper and aluminium conductors as well as laminated copper bars.

Features

| | |
|---|--|
| Model No. | SV 9666.350 |
| Product description | For connecting copper and aluminium conductors. For laminated copper bars or solid and stranded conductors with a pressed wire end ferrule. |
| Material | Duroplastic |
| Colour | RAL 7035 |
| Supply includes | Assembly parts |
| Assembly instruction | Contact hazard protection module 9666.020 is additionally required to cover the connection terminal block. |
| Rated current max. | 400 A |
| Number of poles | 5-pole |
| Connection of round conductors | 50 - 240 2 x 25 - 120 |
| Clamping area for laminated copper bars (W x H) | 25 x 21 mm |
| Packs of | 1 pc(s). |
| Net weight | 4.807 kg |
| Gross weight | 5.08 kg |
| Customs tariff number | 39211900 |
| ETIM 9 | EC001894 |
| ECLASS 8.0 | 27400613 |
| Product description | SV Connection terminal block (ISV), 400 A, 690 V, 5-pole, round conductor connection, 1x50-240/2x25-120 mm ² , clamping area BH: 25x21 mm |

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK