


Rittal – The System.

Faster – better – everywhere.



RX 9360.740

RiLineX component adaptor

State: 5/02/2026 (Source: ittal.com/ie-en)

RX 9360.740 - RiLineX component adaptor

RiLineX component adaptor (45 A, 3-pole, including connection cables) in width 54 mm for 60 mm busbar systems. With fitted support rail for snap-on mounting of equipment and tool-free adjustment.

Features

Model No.	RX 9360.740
Design	With connection cable
Benefits	<p>For mounting equipment for top hat rail installation, e.g. motor starter</p> <p>Pre-assembled connection cable</p> <p>Simple clip locking for support rails</p> <p>Optional anti-slip guard</p> <p>Snap-on mounting and simple adjustment for busbar thickness (5/10 mm)</p> <p>Simple assembly</p> <p>Coordinated accessories reduce the number of different items required</p>
Material	<p>Polyamide (PA 6)</p> <p>Fire protection corresponding to UL 94</p>
Colour	<p>RAL 9005</p> <p>RAL 35745</p>
Connection cables (AWG)	AWG 8
Rated current of round conductor	50 A
Rated current of round conductor (UL)	50 A
Electrical ratings UL (SCCR)	<p>100 kA - 600 V, Fuse Class RK5 max. 60 A, JDDZ/7</p> <p>20 kA - 600 V, circuit breaker max. 60 A, DIVQ/7</p> <p>65 kA - 480 V, Combination Motor Controller max. 52 A, NKJH/7</p>
Cable outlet	Top
For bar systems with centre-to-centre spacing	60 mm

Features

Length of connection cable	130 mm
Number of poles	3-pole
To fit busbar system	RiLineX RiLine60
Dimensions	Width: 54 mm Height: 239.4 mm Depth: 36.2 mm
Support rails Qty/height	1 / 10 mm
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	690 V AC 600 V AC (UL) 600 V DC (UL)
Overvoltage category	4
Contamination level	3
Standards	IEC 61 439-1/-2 UL 508
IP protection category to IEC 60 529	IP 2XB
Operation humidity max	90 %
Operating temperature range	-5 °C...55 °C
Storage temperature range	-25 °C...75 °C
Ambient humidity (non-condensing)	10...90 %
Packs of	4 pc(s).
Net weight	1.68
Gross weight	1.708
Copper weight (kg per piece)	0.101
Customs tariff number	85369095

Features

EAN 4028177997004

ETIM 9 EC001531

Approvals

Approvals UL + C-UL (listed)

Explanations Declaration of conformity