

Rittal – The System.

Faster – better – everywhere.



CS 9791.045

Outdoor wall-mounted enclosures

State: 11/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9791.045 - Outdoor wall-mounted enclosures

Outdoor enclosures for wall or pole mounting. Enclosure-within-an-enclosure concept, outer enclosure with cut-out at the bottom and integrated louvres on the rear panel and side panels for ventilation.



Features

| | |
|---------------------|---|
| Model No. | CS 9791.045 |
| Product description | Outdoor enclosures for wall or pole mounting. Enclosure-within-an-enclosure concept, outer enclosure with cut-out in the bottom and integrated louvres on the rear panel and side panels for ventilation. |
| Material | Enclosure and mounting plate: Aluminium, AlMg3 Door, inner enclosure: Stainless steel 1.4301 (AISI 304) |
| Surface finish | Enclosure: Powder-coated, UV-resistant pure polyester |
| Colour | RAL 7035 |
| Supply includes | Double-walled outdoor enclosure, fully preconfigured Inner enclosure with mounting plate, gland plate and security lock Mounting bracket for enclosure internal thermostat or hygostat Outer enclosure with designer cover and security lock 3524 E 2 C rails on the rear panel 2 security locks |
| Dimensions | Width: 630 mm Height: 780 mm Depth: 380 mm |

Features

| | |
|-------------------------------------|--|
| Clearances | Clearance width: 560 mm Clearance height: 560 mm Clearance depth: 308 mm |
| Dimensions mounting plate (W x H) | 550 mm x 550 mm |
| Inner enclosure | Width: 580 mm Height: 580 mm Depth: 333 mm |
| Lock | Lock version: Cam Number of locks: 2 |
| IP protection category to IEC 60529 | IP 55 |
| Note | Extended delivery times. |
| Basic material | Aluminium |
| Packs of | 1 pc(s). |
| Net weight | 22.254 kg |
| Gross weight | 23.425 kg |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |
| ECLASS 8.0 | 27180101 |
| Product description | CS Wall-mounted enclosure, WHD: 630x780x380 mm, aluminum, with mounting plate, Enclosure-within-an-enclosure concept |

Approvals

| | |
|--------------|---|
| Explanations | Declaration of conformity Declaration of conformity UK |
|--------------|---|

Tender text

Outdoor wall-mounted enclosure

Dual-shell outdoor aluminium enclosure for pole or wall mounting, consists of an outdoor enclosure with louver ventilation, security lock and a lockable interior enclosure with mounting plate.

Interior enclosure: Body: 1.5 mm aluminium, folded and welded from a single piece with protection channel around the door opening. Screwed on gland plate fitted at top (W x D = 302 x 122 mm) and bottom (W x D = 182 x 52 mm). Thermostat mounting holder fitted at top left. Door: 2 mm aluminium, mounted, with foamed-in sealer and screwed on hinges, 180° opening angle, cam lock with security lock Mounting plate: 2 mm aluminium

Outer enclosure: Enclosure with removable cover and security lock design. Ventilation louvers in upper left, right and rear sections; rows of ventilation holes in the left and right side of the base. Screwed on gland plate at the bottom. Two C-rails screwed on at the rear for mounting a pole attachment. Enclosure cover with recessed handle.

Material Interior enclosure, outer enclosure and mounting plate: Aluminium AlMg3

Surface: Interior enclosure and outer enclosure: Powder-coated in RAL 7035 Mounting plate: zinc-plated, passivated

Dimensions: Interior enclosure: W x H x D: 580 x 580 x 333 mm Outer enclosure: W x H x D: 630 x 780 x 380 mm

Protection category: IP 55 to EN 60 529/10.9

Model: Rittal Type: Outdoor wall-mounting enclosure CS Pos. Tender text for outdoor wall-mounted enclosure

Outdoor wall-mounted enclosure

Dual-shell outdoor aluminium enclosure for pole or wall

mounting, consists of an outdoor enclosure with louver ventilation, security lock and a lockable interior enclosure with mounting plate.

Interior enclosure: Body: 1.5 mm aluminium, folded and welded from a single piece with protection channel around the door opening. Screwed on gland plate fitted at top (W x D = 302 x 122 mm) and bottom (W x D = 182 x 52 mm). Thermostat mounting holder fitted at top left. Door: 1,5 stainless steel, mounted, with foamed-in sealer and screwed on hinges, 180° opening angle, cam lock with security lock Mounting plate: 2 mm aluminium

Outer enclosure: Enclosure with removable cover and security lock design. Ventilation louvers in upper left, right and rear sections; rows of ventilation holes in the left and right side of the base. Screwed on gland plate at the bottom. Two C-rails screwed on at the rear for mounting a pole attachment. Enclosure cover with recessed handle.

Material Interior enclosure, outer enclosure and mounting plate: Aluminium AlMg3

Surface: Interior enclosure and outer enclosure: Powder-coated in RAL 7035 Mounting plate: zinc-plated, passivated

Dimensions: Interior enclosure: W x H x D: 580 x 580 x 333 mm Outer enclosure: W x H x D: 630 x 780 x 380 mm

Protection category: IP 55 to EN 60 529/10.9