

# Rittal – The System.

Faster – better – everywhere.



## CS 9888.550

## CS Toptec

State: 11/05/2026 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CS 9888.550 - CS Toptec

Outdoor enclosure with 100 mm transport plinth and rain canopy with projections on all sides. Side panels, rear panel and door fully double-walled on the outside, the entire TS 8 frame is available for interior installation.



## Features

Model No.	CS 9888.550
Design	With cut-out for outdoor cooling units 1.5 kW
Product description	Outdoor enclosure with 100 mm transport plinth and rain canopy with projections on all sides. Side panels, rear panel and door fully double-walled on the outside, the entire TS 8 frame is available for interior installation.
Material	Enclosure frame: Stainless steel 1.4301 (AISI 304) Enclosure panels and base/plinth trim: Aluminium, AlMg3 Rain canopy: Aluminium
Surface finish	Powder-coated UV-resistant pure polyester
Colour	RAL 7035

# Features

Supply includes	Double-walled outdoor enclosure, fully preconfigured Enclosure frame with 25 mm system punchings in the roof and base frame plus vertical sections with two mounting levels Front door with door stay, swing lever handle and profile half-cylinder, lock BJ 20027 Side panels left and right Rear panel Rain canopy Base/plinth with screw-fastened gland plates and screw-fastened trim panels front and rear
Dimensions	Width: 800 mm Height: 1,800 mm Depth: 800 mm
IP protection category to IEC 60529	IP 55
Protection category NEMA	NEMA 3R NEMA 12
IK Code	IK10
Note	All enclosure panels are doubled and earthed (external wall onto internal wall) CS Toptec is the ideal basis for projects in the outdoor sector. It can be requested using these Model Numbers: For stand-alone siting: 9774.099, for baying: 9774.005
Note on Model No.	A climate control unit or adaptor plate is required to seal the cut-out
Basic material	Aluminium
Packs of	1 pc(s).
Net weight	115 kg
Gross weight	122 kg
Customs tariff number	94032080
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	CS TopTec enclosure WHD: 800x1800x800 mm with cut-out for outdoor climate control units 1.5 kW

# Approvals

---

Explanations

Declaration of conformity

## Tender text

Enclosure (Toptec Outdoor Enclosure)

Toptec Outdoor Housing Single door, double wall  
With cut-out for Blue e+ outdoor cooling unit 3185330  
or the use of filters / fans and bulkheading for  
Avoidance of air short circuits in the double wall.  
Outdoor housing with 100 mm transport base/plinth and all sides  
overhanging rain cover. side walls, rear wall and  
Door completely doubled up to the outside, the complete  
TS 8 frame is available for interior installation.  
Double-walled outdoor housing, completely pre-assembled  
TS 8 frame with 25 mm system perforation in  
Roof and floor frames and vertical profiles with  
2 mounting levels  
Front door with door stop, lever handle and  
Profile half cylinder, locking BJ20027  
Side walls left and right  
Rear panel  
Rain cover  
Base with bolted flange plates and bolted  
Front and rear panels  
Door:  
with 4-point lock and Dirak swivel handle with  
ABUS C83N profile half cylinder with lock BJ20027  
Flat parts:  
Roof, door, rear wall, floor panels  
(2 flange plates, size: 340x150 mm)  
included in delivery.  
All flat parts doubled and earthed  
(outer wall to inner wall).  
Material:  
Housing frame: stainless steel 1.4301 (AISI 304)  
Flat parts and plinth panels: Aluminium, AlMg3

Rain cover: aluminium

Surface finish:

Powder-coated

UV-resistant pure polyester

Exterior surfaces powder-coated in RAL 7035 texture outdoor.

Protection class to IEC 60 529: IP 55

Impact protection according to IEC 62 262: IK10

Dimensions (W x H x D): 800x1800x800 mm