

# Rittal – The System.

Faster – better – everywhere.



## RX 9361.300

State: 17/06/2025 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9361.300 -

Connection adaptor for RiLineX busbar platform. To fit double connection (bar). Freely selectable phase difference. Only suitable for 10 mm busbars.



## Features

|   |  |
|---|--|
| Model No.                                       | RX 9361.300  |
| Benefits  | Mounting on the busbar system and cable connection with just one screw   |
| Material  | Polyamide (PA 6)<br>Fire protection corresponding to UL 94   |
| Colour  | RAL 9005   |
| Rated current max.                              | 1,500 A  |
| Electrical ratings UL (SCCR)                    | 52.5 kA - 600 V, RMS<br>100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7<br>100 kA - 600 V, Fuse Class L max. 2000 A, JDDZ/7 |
| Cable outlet                                    | Top/bottom   |
| For bar systems with centre-to-centre spacing   | 60 mm  |
| Number of poles                                 | Single-pole  |
| To fit busbar system                            | RiLineX<br>RiLine60  |
| Dimensions                                      | Width: 73 mm<br>Height: 120 mm<br>Depth: 120 mm  |
| Clamping area for laminated copper bars (W x H) | 50 x 20 mm   |

# Features

|   |  |
|---|--|
| To fit busbars                          | 15 x 5/10<br>20 x 5/10<br>30 x 5/10                        |
| Rated voltage                           | 1,000 V AC<br>1,500 V DC<br>600 V AC (UL)<br>600 V DC (UL) |
| Overvoltage category                    | 4  |
| Contamination level                     | 3  |
| Standards                               | IEC/EN 61439-1<br>UL 508                                   |
| Rated impulse withstand voltage<br>Uimp | 12 kV  |
| Rated insulation voltage                | 1,000 V  |
| IP protection category to IEC 60529     | IP 2XB   |
| Operation humidity max                  | 90 %   |
| Operating temperature range             | -5 °C...55 °C  |
| Storage temperature range               | -25 °C...75 °C   |
| Ambient humidity (non-condensing)       | 10...90 %  |
| Packs of                                | 1 pc(s).   |
| Net weight                              | 0.65   |
| Gross weight                            | 0.688  |
| Customs tariff number                   | 85369010   |
| ETIM 9                                  | EC001531   |

## Approvals

# Approvals

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |