

Rittal – The System.

Faster – better – everywhere.



AE 1017.600

Compact enclosures AE

State: 28/6/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AE 1017.600 - Compact enclosures AE Stainless steel

Compact enclosure AE in stainless steel including mounting plate.

Features

Model No.	AE 1017.600
Material	Enclosure: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Sheet steel Stainless steel 1.4301 (AISI 304)
Surface finish	Enclosure and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated
Supply includes	Enclosure with door(s) Mounting plate Lock: 3 mm double-bit 3-point lock system
Protection category NEMA	NEMA 4X
Protection category to IEC 60 529	IP 66
IK Code	IK08
Dimensions	Width: 800 mm Height: 1,200 mm Depth: 300 mm
Dimensions mounting plate (W x H)	740 mm x 1,155 mm
Number of doors	1
Lock	Lock version: 3-point lock system Number of locks: 1 Lock insert: 3 mm double-bit Material lock: Stainless steel 1.4301 (AISI 304)
Basic material	Stainless steel 1.4301 (AISI 304)
Packs of	1 pc(s).

Features

Net weight	57.8 kg
Gross weight	65.16 kg
Customs tariff number	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	AE Compact enclosure, WHD: 800x1200x300 mm, Stainless steel 1.4301, with mounting plate, single-door, 3-point lock system

Approvals

Approvals	DNV Lloyds Register UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK