

# Rittal – The System.

Faster – better – everywhere.



## KEL 9403.600 Ex enclosures

State: 23/08/2025 (Source: [rittal.com/ie-en](https://www.rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KEL 9403.600 - Ex enclosures Stainless steel, empty enclosure with hinged door

Ex enclosure with hinged door, stainless steel



## Features

Model No.	KEL 9403.600
Design	Ex enclosures
Applications	Zone 1 and 2 or 21 and 22 to 2014/34/EC Ambient temperature range: -30 °C...+80 °C The specified temperatures may be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection thanks to increased safety (Ex e), equipment protection thanks to enclosure (Ex tb)
Material	Enclosure: Stainless steel 1.4301 (AISI 304) Door: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal Mounting plate: Sheet steel
Surface finish	Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated
Supply includes	Enclosure Door Mounting plate

# Features

Dimensions	Width: 380 mm Height: 380 mm Depth: 210 mm
Dimensions mounting plate (W x H)	334 mm x 355 mm
Certificate IEC EX PTB 09.0035U	Yes
Certificate PTB 02 ATEX 1082U	Yes
Basic material	Stainless steel 1.4301 (AISI 304)
Lock	Lock version: Cam Number of locks: 1 Lock insert: 3 mm double-bit
IP protection category to IEC 60529	IP 66
Protection category NEMA	NEMA 4X
Type rating to UL 50E	Type 1 Type 4 Type 4X Type 12
Packs of	1 pc(s).
Net weight	9.6
Gross weight	9.8
Customs tariff number	94032080
EAN	4028177138742
ETIM 9	EC002503
ECLASS 8.0	27180502

## Approvals

# Approvals

---

Approvals

ATEX  
CQC-CCC  
IEC Ex  
UL + C-UL (listed)

---

Explanations

Manufacturer's declaration