

Rittal – The System.

Faster – better – everywhere.



SZ 2411.871

Cable gland, brass

State: 8/7/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.871 - Cable gland, brass

Integrated clamping membrane ensure safe tightening and cable-friendly strain relief.

Features

Model No.	SZ 2411.871
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables
Material	Brass Seal: CR/NBR
Surface finish	Nickel-plated
IP protection category to IEC 60529	IP 68 (5 bar, 30 min)
Dimensions	Height: 54 mm
Thread	M63 x 1.5
Thread length	14 mm
Min. cable diameter	34 mm
Max. cable diameter	44 mm
Operating temperature range	-40 °C...100 °C
torque	50 Nm
Width across flats	64 mm
Dimensions	Thread: M63 x 1.5 Thread length: 14 mm
Type rating to UL 50E	Type 1 Type 4 Type 4X Type 12 Type 13
Packs of	1 pc(s).

Features

Net weight	0.48 kg
Gross weight	0.498 kg
Customs tariff number	74198090
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Product description	SZ Cable gland, brass, size: M63x1,5, for cables ø 34-44 mm

Approvals

Approvals	UL + C-UL (listed) VDE
Explanations	Declaration of conformity Declaration of conformity UK
