


Rittal – The System.

Faster – better – everywhere.



SZ 2482.330

**Mounting frame, interface flap,
modular**

State: 30/5/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2482.330 - Mounting frame, interface flap, modular

Suitable for universal use, for rapid access to interfaces and sockets, the affected enclosure remains closed.

Features

| | |
|----------------------|--|
| Model No. | SZ 2482.330 |
| Design | Mounting frame, double, with metal flap |
| Product description | For universal use in all situations where rapid access to interfaces and sockets is needed. The affected enclosure remains closed and is therefore protected from ambient influences and unauthorised access. |
| Function principle | The mounting frame has a flap which snaps into position in various stages at opening angles of 90 to 180°. A snap fastener ensures reliable sealing. This may be locked if required. |
| Material | Lock: Polycarbonate Mounting frame and metal flap: Fine die-cast zinc |
| Surface finish | Mounting frame and metal flap: Matt nickel-plated |
| Colour | Lock: RAL 7024 Screw terminals: yellow (RAL 1016) |
| Mounting cut-out | Cut-out width: 117 mm Cut-out height: 91 mm |
| Installation options | In small and compact enclosures as a programming interface for controllers In IT and industrial distributors as maintenance access for networks In PC enclosures and console systems for the temporary connection of additional equipment in mobile Industrial Workstations for rapid connection to existing network structures In command panel systems for programming and maintenance of integral components. |
| Dimensions | Width: 130 mm Height: 120 mm |

Features

| | |
|-------------------------------------|--|
| IP protection category to IEC 60529 | IP 65 with sealed flap and proper assembly |
| Packs of | 1 pc(s). |
| Net weight | 0.619 |
| Gross weight | 0.627 |
| Customs tariff number | 85369095 |
| EAN | 4028177490680 |
| ETIM 9 | EC002625 |
| ETIM 8 | EC002625 |
| ECLASS 8.0 | 27189234 |

Approvals

| | |
|--------------|--------------------------------|
| Approvals | C-UR UR + C-UR (recognized) |
| Explanations | Declaration of conformity |