

# Rittal – The System.

Faster – better – everywhere.



## VX 9666.916

## Bayed enclosure system VX25

State: 3/08/2025 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 9666.916 - Bayed enclosure system VX25 Distribution enclosure

Baying systems VX as distribution enclosures, prepared for ISV installation modules



## Features

Model No.	VX 9666.916
Material	Sheet steel
Surface finish	Enclosure frame: Dipcoat-primed Door(s), roof, rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Gland plates: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure frame Door(s) Door hinged on the right, may be swapped to the left Gland plates Rear panel Roof plate Lock: 3 mm double-bit
Number of doors	1
Note	For 600 mm wide distribution enclosures, please use VX basic enclosures For a base/plinth height of 200 mm, 2 packs each of plinth corner pieces, 100 mm and base/plinth trim panels, 100 mm are required

# Features

IP protection category to IEC 60529	IP 55
Protection category NEMA	NEMA 12
Test specification	IEC 61 439-1/-2
Dimensions	Width: 850 mm Height: 2,000 mm Depth: 600 mm
Packs of	1 pc(s).
Net weight	89.2
Gross weight	91.6
PCF per pack (cradle-to-gate)	288.3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94032080
EAN	4028177929722
ETIM 9	EC000214
ECLASS 8.0	27142409

# Approvals

Approvals	Bureau Veritas DNV-GL
Certificates	Surface finish
Explanations	Declaration of conformity Declaration of conformity UK