## Rittal - The System.

Faster – better – everywhere.





# SV 9677.165 NH slimline switch-disconnector

State: 30/10/2025 (Source: rittal.com/ie-en)



## SV 9677.165 - NH slimline switch-disconnector

3-pole, for bar systems with 185 mm centre-to-centre spacing.

#### **Features**

Model No.	SV 9677.165
Design	3-pole, switchable
Function principle	Automatic quick-break contact allows operator-independent switching  Double-break for reliable disconnection of the contacts
Material	Polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Partially silver-plated hard copper
Colour	Chassis: RAL 7035 Cover: RAL 7001 Handle: RAL 7016
For NH size	1
For bar systems with centre-to- centre spacing	185 mm
Cable outlet	Тор
Type of electrical connection	Screw M12
Installation type	Screw attachment
Number of poles	3-pole
Rated operating voltage	800 V (AC), 3~
Rated operating current max.	250 A
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 100 mm Height: 772 mm
Connection of round conductors	6 - 240 mm²
To fit busbars	Height: 10 mm

© Rittal 2025

## Features

Packs of	1 pc(s).
Net weight	10.84
Gross weight	11.94
Copper weight (kg per piece)	2.868
Customs tariff number	85361090
EAN	4028177809062
ETIM 9	EC001040
ECLASS 8.0	27371401

## **Approvals**

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3