

# Rittal – The System.

Faster – better – everywhere.



## SV 9677.920 Connection block

State: 26/05/2024 (Source: [rittal.com/ie-en](https://www.rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9677.920 - Connection block

For connecting cables and laminated copper bars.

## Features

Model No.	SV 9677.920
Product description	For connecting cables and laminated copper bars.
Material	Sheet steel, zinc-plated E-Cu, tin-plated
Cable outlet	Top/bottom
Type of electrical connection	Ring terminal M12
Rated current max.	1,600 A
Dimensions	Width: 98 mm
Connection for round conductor cross-sections	240 mm²
To fit busbars	Height: 10 mm
Packs of	1 pc(s).
Weight/pack	1.66 kg
Copper weight (kg per piece)	1.471
Customs tariff number	85369095
EAN	4028177806351
ETIM 7.0	EC001900
ECLASS 8.0	27400613

## Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------

# Approvals

---

Explanations	Declaration of conformity
	Declaration of conformity UK