

Rittal – The System.

Faster – better – everywhere.



VX 9680.426 Modular enclosure

State: 7/07/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 9680.426 - Modular enclosure Bayed enclosure system VX25

Baying systems VX, for installation with partial doors and internal separation in a modular design.

Features

Model No.	VX 9680.426
Material	Sheet steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Gland plates: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure frame Rear panel Gland plates
Protection category to IEC 60 529	Up to IP 54, depending on the panels
Test specification	IEC 61 439-1/-2 IEC 61 641
Dimensions	Width: 400 mm Height: 2,200 mm Depth: 600 mm
Packs of	1 pc(s).
Net weight	36 kg
Gross weight	38.5 kg
PCF per pack (cradle-to-gate)	106.4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94032080
ETIM 9	EC000261

Features

ECLASS 8.0

27180101

Product description

VX Modular enclosure, WHdepth 400x2200x600 mm, sheet steel

Approvals

Certificates

Surface finish