


Rittal – The System.

Faster – better – everywhere.



VX 9680.608

Bayed enclosure system VX25

State: 28/06/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 9680.608 - Bayed enclosure system VX25 Modular enclosure

Baying systems VX, for installation with partial doors and internal separation in a modular design.

Features

| | |
|-----------------------------------|--|
| Model No. | VX 9680.608 |
| Material | Sheet steel, 1.5 mm |
| Surface finish | Enclosure frame: Dipcoat-primed Rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Gland plates: Zinc-plated |
| Colour | RAL 7035 |
| Supply includes | Enclosure frame Rear panel Gland plates |
| Protection category to IEC 60 529 | Up to IP 54, depending on the panels |
| Test specification | IEC 61 439-1/-2 IEC 61 641 |
| Dimensions | Width: 600 mm Height: 2,000 mm Depth: 800 mm |
| Packs of | 1 pc(s). |
| Net weight | 44.7 kg |
| Gross weight | 49.2 kg |
| PCF per pack (cradle-to-gate) | 132.3 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |

Features

ECLASS 8.0

27180101

Product description

VX Modular enclosure, WHdepth 600x2000x800 mm, sheet steel

Approvals

Certificates

Surface finish