

Rittal – The System.

Faster – better – everywhere.



SV 9690.023

Energy storage enclosure

State: 13/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9690.023 - Energy storage enclosure VX ESS

Enclosure frame with roof plate, perforated door and rear panel. Ideal for efficient and modular energy storage installation with component shelves.

Features

| | |
|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | SV 9690.023 |
| Design | Without interior fit-out |
| Material | Enclosure frame: Sheet steel, 1.5 mm Roof plate: Sheet steel, 1.5 mm Door: Sheet steel, 1.5 mm Rear panel: Sheet steel, 1.5 mm |
| Surface finish | Enclosure frame: Dipcoat-primed Door, roof and rear panel: Powder-coated, textured paint |
| Colour | RAL 7035 |
| Supply includes | Enclosure frame Door and rear panel, perforated Roof plate Lock: 3 mm double-bit |
| Protection category to IEC 60 529 | IP 20 |
| Dimensions | Width: 800 mm Height: 2,000 mm Depth: 800 mm |
| Packs of | 1 pc(s). |
| Net weight | 67 kg |
| Gross weight | 67.7 kg |
| PCF per pack (cradle-to-gate) | 221.54 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94032080 |
| ETIM 9 | EC000261 |

Features

Product description

VX ESS energy storage enclosure WxHxD: 800x2000x800 with door, rear panel

Approvals

Explanations

Declaration of conformity