

Rittal – The System.

Faster – better – everywhere.



SK 3201.830

Modular climate control concept – climate control door VX25

State: 8/12/2025 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3201.830 - Modular climate control concept – climate control door VX25 for installing cooling modules

Sheet steel climate control doors for the installation of climate control module types SK 3307.7XX to 3310.7XX.

Features

Model No.	SK 3201.830
Product description	Sheet steel climate control doors for the installation of climate control module types SK 3307.7XX to 3310.7XX. The climate control doors fit perfectly with the overall design of the enclosure.
Material	Sheet steel
Colour	RAL 7035
Supply includes	Climate control door without preconfigured cooling module 180° hinges, door opening angle approx. 130°
Note on Model No.	To fit VX enclosures For 1200 mm wide VX enclosures, the existing hinged door may be used, irrespective of the device position (left or right) R/h door hinge
To fit	Enclosure type: VX: = 800 mm: = 2,000 mm
Packs of	1 pc(s).
Net weight	38
Gross weight	42.2
EAN	4028177925731
ETIM 9	EC002510
ETIM 8	EC002510
ECLASS 8.0	27180702

Approvals

Certificates	EAC
Explanations	Declaration of conformity - F-gas regulation

Tender text

SK 3201.830

Modular climate control concept – climate control door VX25 for installing cooling modules

Sheet steel climate control doors for the installation of climate control module types SK 3307.7XX to 3310.7XX. The climate control doors fit perfectly with the overall design of the enclosure.

Material: Sheet steel

Colour: RAL 7035

To fit VX enclosures

Dimensions WxH [mm]: 800x2000

door hinge right