## Rittal – The System.

Faster – better – everywhere.





# AE 1019.500 Compact enclosures AE

State: 8/12/2025 (Source: rittal.com/in-en)



## AE 1019.500 - Compact enclosures AE Stainless steel

Compact enclosure AE in stainless steel including mounting plate.

#### **Features**

Model No.	AE 1019.500
Material	Enclosure: Stainless steel
	Door: Stainless steel, all-round foamed-in PU seal
	Mounting plate: Sheet steel
	Stainless steel 1.4404 (AISI 316L)
Surface finish	Enclosure and door: Brushed, grain 400, peak-to-valley height
	< 0.8 μm
	Mounting plate: Zinc-plated
Supply includes	Enclosure with door(s)
	Mounting plate
	Lock: 3 mm double-bit
	3-point lock system
Protection category NEMA	NEMA 12
Protection category to IEC 60 529	IP 55
IK Code	IK08
Dimensions	Width: 1,000 mm
	Height: 1,200 mm
	Depth: 300 mm
Dimensions mounting plate (W x H)	940 mm x 1,155 mm
Number of doors	2
Lock	Lock version: 3-point lock system
	Number of locks: 1
	Lock insert: 3 mm double-bit
	Material lock: Stainless steel 1.4301 (AISI 304)
Basic material	Stainless steel 1.4404 (AISI 316L)

© Rittal 2025

#### **Features**

Net weight	76.4
Gross weight	79.5
Customs tariff number	94032080
EAN	4028177421394
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

# Approvals

DNV-GL UL + C-UL (listed)
Declaration of conformity  Declaration of conformity UK

© Rittal 2025 3