

# Rittal – The System.

Faster – better – everywhere.



## SG 2371.010

### Flashing light component

State: 6/7/2025 (Source: [rittal.com/in-en](https://www.rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2371.010 - Flashing light component for signal pillar, modular

With 360° signal transmission thanks to optimised prism system, number of potential stages = 5 components, with identical voltage.



## Features

Model No.	SG 2371.010
Design	Flashing light component
Product description	With 360° signal transmission thanks to optimised prism system. Number of potential stages = 5 components, with identical voltage.
Benefits	Simple assembly and contact via bayonet fastener. Configuration of up to five components with the same voltage. Components are available in a range of colours and voltages. Flashing and stroboscopic light element incl. lamp, suitable for direct use.
Function principle	A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel
Material	Enclosure of polyamide Cap: Transparent polycarbonate
Colour	Green
Diameter	70 mm
Rated impulse withstand voltage, phase to phase	2500 V AC
Rated insulation voltage	250 V AC

# Features

Rated current max.	125 mA
Dimensions	Height: 56 mm
Protection category to IEC 60 529	IP 54 if a cover or acoustic component is fitted at the top
Rated operating voltage	24 V (DC)
Packs of	1 pc(s).
Net weight	0.09
Gross weight	0.097
Customs tariff number	85311095
EAN	4028177220089
ECLASS 8.0	27371220

# Approvals

Approvals	UL + C-UL (listed) UR
-----------	--------------------------