

Rittal – The System.

Faster – better – everywhere.



SZ 2411.611

Cable gland, polyamide

State: 11/2/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.611 - Cable gland, polyamide

Integrated clamping membranes ensure reliable tightening and strain relief to protect the cables.

Features

Model No.	SZ 2411.611
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables
Material	Polyamide 6 Seal: CR/NBR
Colour	RAL 7035
IP protection category to IEC 60 529	IP 68 (5 bar, 30 min)
Dimensions	Height: 30 mm
Thread	M16 x 1.5
Thread length	10 mm
Min. cable diameter	5 mm
Max. cable diameter	10 mm
Operating temperature range	-30 °C...100 °C
torque	2.5 Nm
Width across flats	22 mm
Dimensions	Thread: M16 x 1.5 Thread length: 10 mm
Type rating to UL 50E	Type 4X
Packs of	50 pc(s).
Net weight	0.5
Gross weight	0.546

Features

Customs tariff number 39269097

EAN 4028177810006

ETIM 9 EC000441

ETIM 8 EC000441

ECLASS 8.0 27149109

Approvals

Approvals CSA + CSAus
UR + C-UR (recognized)
VDE

Explanations Declaration of conformity
Declaration of conformity UK