## Rittal – The System.

Faster – better – everywhere.





# SK 3314.030 Touchscreen display, colour

State: 8/12/2025 (Source: rittal.com/in-en)



## SK 3314.030 - Touchscreen display, colour for LCP Rack/ Inline CW

All relevant operating parameters are displayed directly on the LCP display, to allow directly monitoring of key LCP functions and the implementation of settings.





#### **Features**

SK 3314.030
The display offers the opportunity of directly monitoring key functions of the LCP, and implementing settings.
Plastic
RAL 9005
Touchscreen display, colour Assembly parts
SK 3314XX8 (UL version): Units are supplied as standard with the display. SK 3314XX0 (CE version): From serial number 2025K000110475 onwards (production date: 16 September 2025), only display 3314030 may be used as an accessory.
SK 3314.130/230/238/250/260/268/530/538/540/542/548/550/560/5 68/570 SK 3314.020/025
1 pc(s).
0.27
0.307
85312040

© Rittal 2025 2

### **Features**

EAN	4028177984950
ECLASS 8.0	27180712

© Rittal 2025 3

#### Tender text

Tender text Touch-Screen Display, SK3314.030 for LCP Rack / Inline CW SK3314.130/230/238/250/260/268/530/538/540/542/548/560/568/570 and LCP Rear Door CW active modules SK3314.020/025

Touch screen display, colour, SK3314.030

The display shows the user all relevant operating parameters directly on the LCP.

This has the advantage that the status of the device can be recognised quickly and at a glance, if necessary, the user can react and change parameters as quickly as possible.

The following parameters can be read and changed at various levels:

- ·Display of the cold air temperature supplied to the 19' equipment
- ·Display of the hot air temperature discharged from the 19' equipment
- ·Display of control mode (automatic, manual, remote)
- ·Configuration menu: Air Circuit, Coolant circuit, Condensate management, Fan Registry
- ·Cooling water flow temperature / return temperature
- ·Cooling water flow rate
- ·Position of the control valve
- ·Display of pPUE, EER and Cap (cooling capacity)
- ·Overview of all parameters and the option to change them (PIN-protected)
- ·Display of alarm and warning messages
- ·Overview page with IP address of the device, software version and contact person etc. (can be entered individually)

Touch screen display, packaging unit consisting of:

- ·Colour touch-screen display, incl. mounting accessories
- 4.3' display, 480 x 272 pixels
- Resistive touch
- Brightness 200 cd/m<sup>2</sup>
- Storage temperature: -20°C to +70°C
- Earthing cable

© Rittal 2025 4