

# Rittal – The System.

Faster – better – everywhere.



## SK 3328.540

# TopTherm wall-mounted cooling unit Blue e

State: 23/5/2026 (Source: [rittal.com/in-en](http://rittal.com/in-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3328.540 - TopTherm wall-mounted cooling unit Blue e 0.3 - 4 kW

Energy-efficient Blue e wall-mounted cooling units in the output categories 300 W to 4000 W and with integral electrical condensate evaporator (from 1000 W). Available in the special formats "horizontal" and "flat".

## Features

Model No.	SK 3328.540
Design	wall-mounted
Product description	Energy-efficient Blue e wall-mounted cooling units in the output categories 300 W to 4000 W and with integral electrical condensate evaporator (from 1000 W).
Benefits	May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller
Material	Sheet steel
Colour	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Fully wired ready for connection (plug-in terminal strip) Drilling template Assembly parts Integral electric condensate evaporation
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 2.05 kW Cooling output L35 L35/60 Hz: 2.25 kW Cooling output L35 L50/50 Hz: 1.35 kW Cooling output L35 L50/60 Hz: 1.5 kW
Rated operating voltage	400 V, 3~, 50 Hz 460 V, 3~, 60 Hz
Rated current max.	At 50 Hz: 2.2 A At 60 Hz: 2.4 A
Start-up current max.	At 50 Hz: 4.8 A At 60 Hz: 5.5 A

# Features

Air throughput (unimpeded air flow)	External circuit: 900 m <sup>3</sup> /h Internal circuit: 900 m <sup>3</sup> /h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 2.25 Refrigeration factor L35 L35 (EER) 60 Hz: 1.95
Design	wall-mounted
Dimensions	Width: 400 mm Height: 1,580 mm Depth: 295 mm
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54
Protection category NEMA	UL Type 12
Refrigerant/cooling medium	Refrigerant: R-513A Quantity: 0.95 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 0.6 t
Temperature control	e-Comfort controller (factory setting +35 °C)
Operating temperature range	10 °C...55 °C
Storage temperature range	-40 °C...70 °C
Setting range	20 °C...55 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 0.92 kW Power consumption L35 L35/60 Hz: 1.15 kW Power consumption L35 L50/50 Hz: 1.15 kW Power consumption L35 L50/60 Hz: 1.3 kW
Permissible operating pressure (p. max.)	28 bar
Pre-fuse	Motor circuit-breaker: 6.3...10 A
Packs of	1 pc(s).
Net weight	67.45 kg
Gross weight	71 kg
Customs tariff number	84158200
ETIM 9	EC000855

# Features

---

ETIM 8	EC000855
ECLASS 8.0	27180704
Product description	SK cooling unit Blue e, wall-mounted, 2.2 kW, 400/460 V, 3~, 50/60 Hz, Sheet steel, WHD: 400 x 1580 x 295 mm

---

# Approvals

---

Approvals	30 - KC Korea UL + C-UL (listed) UL + C-UL - FTTA UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity - F-gas regulation Declaration of conformity UK

---