

Rittal – The System.

Faster – better – everywhere.



SK 3212.230

Air/water heat exchangers

State: 21/5/2026 (Source: rittal.com/in-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3212.230 - Air/water heat exchangers wall-mounted

Output classes 375 – 5,000 W. For use in tough environments. Convenient mounting options and flexible water connection options. External mounting or full internal mounting possible.

Features

| | |
|--|--|
| Model No. | SK 3212.230 |
| Design | wall-mounted Water-carrying parts, copper/brass (Cu/CuZn) |
| Product description | For use in harsh environments and temperature ranges up to +70 °C. User-friendly assembly plus flexible water connection options. External mounting or full internal mounting are supported. |
| Colour | RAL 7035 |
| Supply includes | Fully wired ready for connection Drilling template Sealing and assembly parts |
| Total cooling output | L 35 W 10 at 200 l/h: 0.3 kW |
| Rated operating voltage | 230 V, 1~, 50 Hz/60 Hz |
| Power consumption Pel | At 50 Hz: 23 W At 60 Hz: 27 W |
| Rated current max. | At 50 Hz: 0.11 A At 60 Hz: 0.13 A |
| Permissible operating pressure (p. max.) | 1: 10 bar |
| Duty cycle | 100 % |
| Cooling medium | Water (see Internet for specifications) |
| Water inlet temperature | 1 °C...30 °C |
| Water connections | 3/8" connector sleeve |
| Operating temperature range | 1 °C...70 °C |
| Note | Integral non-return valve for version with e-Comfort controller |

Features

| | |
|-----------------------------------|---|
| Dimensions | Width: 150 mm Height: 300 mm Depth: 85 mm |
| Pre-fuse | Miniature circuit-breaker/fuse: 2 A |
| Setting range | 20 °C...55 °C |
| Protection category to IEC 60 529 | IP 55 |
| Packs of | 1 pc(s). |
| Net weight | 3.227 kg |
| Gross weight | 3.427 kg |
| Customs tariff number | 84158300 |
| ETIM 9 | EC002515 |
| ETIM 8 | EC002515 |
| ECLASS 8.0 | 27180712 |
| Product description | SK Air/water heat exchanger, wall-mounted, 0.3 kW, 230 V, 1~, 50/60 Hz, Water-carrying parts: copper/brass , WHD: 150 x 300 x 85 mm |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|

Tender text

Wall-mounted air/water heat exchanger

For use in tough environments. Flexible water connection options.

Total cooling output L 35 W 10, 200l/h: 0.3 kW

Rated operating voltage: 230 V, 50/60 Hz

Refrigerant: Water (see specifications)

Water-carrying parts: Cu/CuZn

Dimensions [W x H x D]: 150 x 300 x 85 mm

Ambient temperature range: 1°C to 70°C

Water inlet temperature range: 1°C to 30°C

Type of connection: Plug-in terminal strip

Protection category to IEC 60 529: IP 55

Weight: 3.2 kg

Colour: RAL 7035