
## Rittal – The System.

Faster - better - everywhere.





# SV 3453.500 Conductor connection clamp

State: 5/11/2025 (Source: rittal.com/in-en)



## SV 3453.500 - Conductor connection clamp

For connecting round conductors and laminated copper bars.

#### **Features**

Model No.	SV 3453.500
Product description	For connecting round conductors and laminated copper bars.
Material	Sheet steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	16.5 x 15 mm
Note	Wire end ferrules should be used with fine wire conductors
Connection of round conductors	35 - 70 mm²
For bar thickness	5 mm
Packs of	15 pc(s).
Net weight	1.515
Gross weight	1.62
PCF per pack (cradle-to-gate)	6.4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	85369010
EAN	4028177042704
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146

© Rittal 2025

### **Approvals**

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity
	Declaration of conformity UK

#### Tender text

SV conductor connection clamps for E-CU busbars and Rittal PLS.

For bar thickness: 5 mm

Connection of round conductors: 35 - 70 mm2

Wire end ferrules should be used with

fine wire conductors.

Clamping area: for laminated copper

bars 16.5 x 15 mm Tightening torque

Conductor connection clamp: 10-12 Nm Material: sheet steel, zinc-plated, passivated

© Rittal 2025